

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1303829

Luminaire Tested: P3RT09R709050DE010 E3CBUS1MW

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1303829  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-95)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3RT09R709050DE010 E3CBUS1MW  
Description: 3in Adjustable LED luminaire with, R70 optic, 5000K CCT AND, 90CRI , E3CBUS1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1003.0 lumens  
Efficiency: N/A  
Efficacy: 90.4 lumens/watt  
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.99  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1303829

CATALOG NUMBER: P3RT09R709050DE010 E3CBUS1MW

### Luminous Intensity Polar Plot



TEST NUMBER: P1303829

CATALOG NUMBER: P3RT09R709050DE010 E3CBUS1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 30  |     |     |  |     | 10  |     |  |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |
| 1   | 114 | 111 | 108 | 106 |  | 111 | 109 | 107 | 105 |  | 105 | 103 | 101 |  | 101 | 100 | 98  |  | 98  | 96  | 95  |
| 2   | 108 | 103 | 99  | 96  |  | 106 | 102 | 98  | 95  |  | 98  | 95  | 93  |  | 95  | 93  | 91  |  | 93  | 91  | 89  |
| 3   | 103 | 96  | 91  | 88  |  | 101 | 95  | 90  | 87  |  | 92  | 89  | 85  |  | 90  | 87  | 84  |  | 88  | 85  | 83  |
| 4   | 98  | 90  | 85  | 80  |  | 96  | 89  | 84  | 80  |  | 87  | 82  | 79  |  | 85  | 81  | 78  |  | 83  | 80  | 77  |
| 5   | 93  | 84  | 79  | 74  |  | 91  | 83  | 78  | 74  |  | 82  | 77  | 73  |  | 80  | 76  | 73  |  | 78  | 75  | 72  |
| 6   | 88  | 79  | 73  | 69  |  | 86  | 78  | 73  | 69  |  | 77  | 72  | 68  |  | 75  | 71  | 68  |  | 74  | 70  | 67  |
| 7   | 83  | 74  | 68  | 64  |  | 82  | 74  | 68  | 64  |  | 72  | 67  | 64  |  | 71  | 67  | 63  |  | 70  | 66  | 63  |
| 8   | 79  | 70  | 64  | 60  |  | 78  | 69  | 64  | 60  |  | 68  | 63  | 59  |  | 67  | 62  | 59  |  | 66  | 62  | 59  |
| 9   | 75  | 66  | 60  | 56  |  | 74  | 65  | 60  | 56  |  | 64  | 59  | 56  |  | 63  | 59  | 55  |  | 63  | 58  | 55  |
| 10  | 72  | 62  | 56  | 52  |  | 71  | 62  | 56  | 52  |  | 61  | 56  | 52  |  | 60  | 55  | 52  |  | 59  | 55  | 52  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 243928 |
| 5°  | 232247 |
| 10° | 222196 |
| 15° | 211965 |
| 20° | 195994 |
| 25° | 177615 |
| 30° | 153365 |
| 35° | 137969 |
| 40° | 53643  |
| 45° | 0      |
| 50° | 0      |
| 55° | 0      |
| 60° | 0      |
| 65° | 0      |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 0 cd/sqm

TEST NUMBER: P1303829

CATALOG NUMBER: P3RT09R709050DE010 E3CBUS1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 98.9   | 9.9       |
| 10°-20°   | 260.8  | 26.0      |
| 20°-30°   | 333.7  | 33.3      |
| 30°-40°   | 288.1  | 28.7      |
| 40°-50°   | 21.4   | 2.1       |
| 50°-60°   | 0.0    | 0.0       |
| 60°-70°   | 0.0    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 693.5  | 69.1      |
| 0°-40°    | 981.6  | 97.9      |
| 0°-60°    | 1003.0 | 100.0     |
| 0°-90°    | 1003.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1003.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1112 |      |
| 5°  | 1055 | 99   |
| 15° | 934  | 261  |
| 25° | 734  | 334  |
| 35° | 515  | 288  |
| 45° | 0    | 21   |
| 55° | 0    | 0    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |

TEST NUMBER: P1303829

CATALOG NUMBER: P3RT09R709050DE010 E3CBUS1MW

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1112.4 |
| 2.5°  | 1095.1 |
| 5°    | 1055.1 |
| 7.5°  | 1020.4 |
| 10°   | 997.9  |
| 12.5° | 970.1  |
| 15°   | 933.7  |
| 17.5° | 890.3  |
| 20°   | 839.9  |
| 22.5° | 784.4  |
| 25°   | 734.1  |
| 27.5° | 669.9  |
| 30°   | 605.7  |
| 32.5° | 579.6  |
| 35°   | 515.4  |
| 37.5° | 374.9  |
| 40°   | 187.4  |
| 42.5° | 24.3   |
| 45°   | 0.0    |
| 47.5° | 0.0    |
| 50°   | 0.0    |
| 52.5° | 0.0    |
| 55°   | 0.0    |
| 57.5° | 0.0    |
| 60°   | 0.0    |
| 62.5° | 0.0    |
| 65°   | 0.0    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |

(END OF REPORT)