

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1305039

Luminaire Tested: P3RT13R30B2750DE010 E3CBUS1MW_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1305039
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-88)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3RT13R30B2750DE010 E3CBUS1MW_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R30 optic, 3000K CCT AND, 90CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1051.0 lumens
Efficiency: N/A
Efficacy: 55.0 lumens/watt
Spacing Criteria (0/90/45): 0.5 / 0.5 / 0.45
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1305039

CATALOG NUMBER: P3RT13R30B2750DE010 E3CBUS1MW_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1305039

CATALOG NUMBER: P3RT13R30B2750DE010 E3CBUS1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	111	110		113	111	109	108		107	106	105		103	103	102		100	99	99
2	112	108	105	103		110	107	104	102		104	101	100		101	99	98		98	97	96
3	108	104	101	98		107	103	100	97		100	98	96		98	96	94		96	94	93
4	105	100	97	94		104	99	96	93		97	94	92		95	93	91		94	92	90
5	102	97	93	90		101	96	93	90		95	91	89		93	90	88		92	89	88
6	100	94	90	87		99	93	90	87		92	89	86		91	88	86		90	87	85
7	97	91	87	84		96	91	87	84		90	86	84		89	86	83		88	85	83
8	95	89	85	82		94	88	84	82		87	84	82		86	83	81		86	83	81
9	92	86	82	80		92	86	82	80		85	82	79		84	81	79		84	81	79
10	90	84	80	78		90	84	80	78		83	80	77		82	79	77		82	79	77

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	942753
5°	916000
10°	775270
15°	466949
20°	168155
25°	47253
30°	12458
35°	4845
40°	1889
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1305039

CATALOG NUMBER: P3RT13R30B2750DE010 E3CBUS1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	376.5	35.8
10°-20°	547.3	52.1
20°-30°	113.0	10.8
30°-40°	13.2	1.3
40°-50°	0.9	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1036.9	98.7
0°-40°	1050.1	99.9
0°-60°	1051.0	100.0
0°-90°	1051.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1051.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4299	
5°	4161	377
15°	2057	547
25°	195	113
35°	18	13
45°	0	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1305039

CATALOG NUMBER: P3RT13R30B2750DE010 E3CBUS1MW_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	4299.3
2.5°	4264.8
5°	4161.4
7.5°	3933.2
10°	3481.8
12.5°	2833.4
15°	2056.9
17.5°	1316.5
20°	720.6
22.5°	361.1
25°	195.3
27.5°	106.7
30°	49.2
32.5°	29.5
35°	18.1
37.5°	11.5
40°	6.6
42.5°	1.6
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)