

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1305044

Luminaire Tested: P3RT13R35B2750DE010 E3CBUS1MW_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1305044
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-89)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3RT13R35B2750DE010 E3CBUS1MW_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R35 optic, 3000K CCT AND, 90CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1055.0 lumens
Efficiency: N/A
Efficacy: 55.2 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.5
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1305044

CATALOG NUMBER: P3RT13R35B2750DE010 E3CBUS1MW_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1305044

CATALOG NUMBER: P3RT13R35B2750DE010 E3CBUS1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	113	111	109	108	107	105	104	103	102	101	100	99	98	97		
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	93		
3	108	103	99	97	106	102	98	96	99	97	94	97	95	93	95	93	92	90		
4	104	99	95	92	103	98	94	92	96	93	90	94	92	89	92	90	89	87		
5	101	95	91	88	100	94	91	88	93	90	87	91	89	86	90	88	86	85		
6	98	92	88	85	97	91	87	85	90	87	84	89	86	83	88	85	83	82		
7	95	89	85	82	94	88	84	82	87	84	81	86	83	81	85	83	80	79		
8	93	86	82	79	92	86	82	79	85	81	79	84	81	78	83	80	78	77		
9	90	83	79	77	89	83	79	76	82	79	76	82	78	76	81	78	76	75		
10	88	81	77	74	87	81	77	74	80	76	74	79	76	74	79	76	74	73		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	772855
5°	749811
10°	668591
15°	472330
20°	227823
25°	73843
30°	20763
35°	8352
40°	2347
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 0 cd/sqm

TEST NUMBER: P1305044

CATALOG NUMBER: P3RT13R35B2750DE010 E3CBUS1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	312.8	29.7
10°-20°	549.9	52.1
20°-30°	169.0	16.0
30°-40°	22.0	2.1
40°-50°	1.4	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1031.7	97.8
0°-40°	1053.7	99.9
0°-60°	1055.0	100.0
0°-90°	1055.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1055.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3524	
5°	3406	313
15°	2081	550
25°	305	169
35°	31	22
45°	0	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1305044

CATALOG NUMBER: P3RT13R35B2750DE010 E3CBUS1MW_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	3524.5
2.5°	3496.6
5°	3406.4
7.5°	3257.1
10°	3002.7
12.5°	2605.6
15°	2080.6
17.5°	1509.6
20°	976.3
22.5°	566.1
25°	305.2
27.5°	160.8
30°	82.0
32.5°	49.2
35°	31.2
37.5°	19.7
40°	8.2
42.5°	3.3
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)