

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1305075

Luminaire Tested: P3RT13R65B2750DE010 E3CBUS1MW\_3500K

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1305075  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-94)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3RT13R65B2750DE010 E3CBUS1MW\_3500K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R65 optic, 3500K CCT AND, 80CRI , E3CBUS1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 982.0 lumens  
Efficiency: N/A  
Efficacy: 51.4 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.84  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 19.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1305075

CATALOG NUMBER: P3RT13R65B2750DE010 E3CBUS1MW\_3500K

### Luminous Intensity Polar Plot



TEST NUMBER: P1305075

CATALOG NUMBER: P3RT13R65B2750DE010 E3CBUS1MW\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    | 20 |    |    |    | 20 |    |    |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    |    | 0  |    |    |    | 0  |    |    |    | 0  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |    |    |    |    |    |    |    |    |    |
| 1   | 114 | 111 | 109 | 107 | 111 | 109 | 107 | 105 | 105 | 103 | 102 | 101 | 100 | 99  | 98  | 97  | 96  | 94  |    |    |    |    |    |    |    |    |    |    |    |
| 2   | 109 | 104 | 101 | 97  | 107 | 103 | 99  | 96  | 99  | 97  | 94  | 96  | 94  | 92  | 94  | 92  | 90  | 89  |    |    |    |    |    |    |    |    |    |    |    |
| 3   | 104 | 98  | 93  | 90  | 102 | 96  | 92  | 89  | 94  | 90  | 87  | 92  | 89  | 86  | 89  | 87  | 85  | 83  |    |    |    |    |    |    |    |    |    |    |    |
| 4   | 99  | 92  | 87  | 83  | 97  | 91  | 86  | 83  | 89  | 85  | 82  | 87  | 83  | 81  | 85  | 82  | 80  | 78  |    |    |    |    |    |    |    |    |    |    |    |
| 5   | 94  | 87  | 81  | 77  | 93  | 86  | 81  | 77  | 84  | 80  | 76  | 82  | 79  | 76  | 81  | 78  | 75  | 74  |    |    |    |    |    |    |    |    |    |    |    |
| 6   | 90  | 82  | 76  | 72  | 89  | 81  | 76  | 72  | 80  | 75  | 72  | 78  | 74  | 71  | 77  | 73  | 71  | 69  |    |    |    |    |    |    |    |    |    |    |    |
| 7   | 86  | 77  | 72  | 68  | 85  | 77  | 71  | 68  | 75  | 71  | 67  | 74  | 70  | 67  | 73  | 69  | 67  | 65  |    |    |    |    |    |    |    |    |    |    |    |
| 8   | 82  | 73  | 68  | 64  | 81  | 73  | 67  | 64  | 72  | 67  | 63  | 71  | 66  | 63  | 70  | 66  | 63  | 62  |    |    |    |    |    |    |    |    |    |    |    |
| 9   | 79  | 69  | 64  | 60  | 77  | 69  | 64  | 60  | 68  | 63  | 60  | 67  | 63  | 60  | 66  | 62  | 60  | 58  |    |    |    |    |    |    |    |    |    |    |    |
| 10  | 75  | 66  | 61  | 57  | 74  | 66  | 60  | 57  | 65  | 60  | 57  | 64  | 60  | 57  | 63  | 59  | 56  | 55  |    |    |    |    |    |    |    |    |    |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 287784 |
| 5°  | 271824 |
| 10° | 263700 |
| 15° | 252805 |
| 20° | 229597 |
| 25° | 199729 |
| 30° | 138198 |
| 35° | 80281  |
| 40° | 21211  |
| 45° | 0      |
| 50° | 0      |
| 55° | 0      |
| 60° | 0      |
| 65° | 0      |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 0 cd/sqm

TEST NUMBER: P1305075

CATALOG NUMBER: P3RT13R65B2750DE010 E3CBUS1MW\_3500K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 116.6  | 11.9      |
| 10°-20°   | 309.3  | 31.5      |
| 20°-30°   | 363.2  | 37.0      |
| 30°-40°   | 184.1  | 18.7      |
| 40°-50°   | 8.9    | 0.9       |
| 50°-60°   | 0.0    | 0.0       |
| 60°-70°   | 0.0    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 789.1  | 80.4      |
| 0°-40°    | 973.1  | 99.1      |
| 0°-60°    | 982.0  | 100.0     |
| 0°-90°    | 982.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 982.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1312 |      |
| 5°  | 1235 | 117  |
| 15° | 1114 | 309  |
| 25° | 826  | 363  |
| 35° | 300  | 184  |
| 45° | 0    | 9    |
| 55° | 0    | 0    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |

TEST NUMBER: P1305075

CATALOG NUMBER: P3RT13R65B2750DE010 E3CBUS1MW\_3500K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1312.4 |
| 2.5°  | 1283.7 |
| 5°    | 1234.9 |
| 7.5°  | 1204.6 |
| 10°   | 1184.3 |
| 12.5° | 1157.4 |
| 15°   | 1113.6 |
| 17.5° | 1051.3 |
| 20°   | 983.9  |
| 22.5° | 914.8  |
| 25°   | 825.5  |
| 27.5° | 685.7  |
| 30°   | 545.8  |
| 32.5° | 424.5  |
| 35°   | 299.9  |
| 37.5° | 175.2  |
| 40°   | 74.1   |
| 42.5° | 11.8   |
| 45°   | 0.0    |
| 47.5° | 0.0    |
| 50°   | 0.0    |
| 52.5° | 0.0    |
| 55°   | 0.0    |
| 57.5° | 0.0    |
| 60°   | 0.0    |
| 62.5° | 0.0    |
| 65°   | 0.0    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |

(END OF REPORT)