

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1305076

Luminaire Tested: P3RT13R65B2750DE010 E3CBUS1MW_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1305076
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-94)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3RT13R65B2750DE010 E3CBUS1MW_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R65 optic, 4000K CCT AND, 80CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 973.0 lumens
Efficiency: N/A
Efficacy: 50.9 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.84
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1305076

CATALOG NUMBER: P3RT13R65B2750DE010 E3CBUS1MW_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1305076

CATALOG NUMBER: P3RT13R65B2750DE010 E3CBUS1MW_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	102	102	102	102	102	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	96	96	96	96	96	96	96	96	96	96	96	94
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	94	92	90	94	92	90	94	92	90	94	92	89
3	104	98	93	90	102	96	92	89	94	90	87	92	89	86	89	87	85	89	87	85	89	87	85	89	87	85	89	87	83
4	99	92	87	83	97	91	86	83	89	85	82	87	83	81	85	82	80	85	82	80	85	82	80	85	82	80	85	82	78
5	94	87	81	77	93	86	81	77	84	80	76	82	79	76	81	78	75	81	78	75	81	78	75	81	78	75	81	78	74
6	90	82	76	72	89	81	76	72	80	75	72	78	74	71	77	73	71	77	73	71	77	73	71	77	73	71	77	73	69
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	73	69	67	73	69	67	73	69	67	73	69	65
8	82	73	68	64	81	73	67	64	72	67	63	71	66	63	70	66	63	70	66	63	70	66	63	70	66	63	70	66	62
9	79	69	64	60	77	69	64	60	68	63	60	67	63	60	66	62	60	66	62	60	66	62	60	66	62	60	66	62	58
10	75	66	61	57	74	66	60	57	65	60	57	64	60	57	63	59	56	63	59	56	63	59	56	63	59	56	63	59	55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	285153
5°	269337
10°	261296
15°	250490
20°	227496
25°	197890
30°	136932
35°	79531
40°	21011
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1305076

CATALOG NUMBER: P3RT13R65B2750DE010 E3CBUS1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.5	11.9
10°-20°	306.5	31.5
20°-30°	359.9	37.0
30°-40°	182.4	18.7
40°-50°	8.8	0.9
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	781.8	80.4
0°-40°	964.2	99.1
0°-60°	973.0	100.0
0°-90°	973.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	973.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1300	
5°	1224	115
15°	1103	306
25°	818	360
35°	297	182
45°	0	9
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1305076

CATALOG NUMBER: P3RT13R65B2750DE010 E3CBUS1MW_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1300.4
2.5°	1272.0
5°	1223.6
7.5°	1193.5
10°	1173.5
12.5°	1146.8
15°	1103.4
17.5°	1041.6
20°	974.9
22.5°	906.4
25°	817.9
27.5°	679.4
30°	540.8
32.5°	420.7
35°	297.1
37.5°	173.6
40°	73.4
42.5°	11.7
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)