

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1302933

Luminaire Tested: P3RT02R159024DE010 E3CBUS1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1302933
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-85)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3RT02R159024DE010 E3CBUS1MW
Description: 3in Adjustable LED luminaire with, R15 optic, 2400K CCT AND, 90CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 278.0 lumens
Efficiency: N/A
Efficacy: 77.2 lumens/watt
Spacing Criteria (0/90/45): 0.29 / 0.29 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1302933
CATALOG NUMBER: P3RT02R159024DE010 E3CBUS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1302933
 CATALOG NUMBER: P3RT02R159024DE010 E3CBUS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98	98	98	98
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	96	96	96	96
3	110	106	103	101	109	105	102	100	103	101	99	101	99	97	98	97	96	95	95	95	95
4	108	103	100	98	106	102	100	97	101	98	96	99	97	95	97	96	94	93	93	93	93
5	106	101	98	95	104	100	97	95	99	96	94	97	95	93	96	94	93	92	92	92	92
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90	90	90	90
7	102	97	93	91	101	96	93	91	95	92	90	94	92	90	93	91	90	89	89	89	89
8	100	95	92	89	99	94	91	89	94	91	89	93	90	89	92	90	88	88	88	88	88
9	98	93	90	88	97	93	90	88	92	89	88	91	89	87	91	89	87	86	86	86	86
10	97	92	89	87	96	91	88	86	91	88	86	90	88	86	90	87	86	85	85	85	85

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	594141
5°	469644
10°	216585
15°	62725
20°	20162
25°	7573
30°	2836
35°	883
40°	258
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 52.5°
 Luminance: 180 cd/sqm



TEST NUMBER: P1302933
 CATALOG NUMBER: P3RT02R159024DE010 E3CBUS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.7	59.6
10°-20°	93.2	33.5
20°-30°	16.4	5.9
30°-40°	2.5	0.9
40°-50°	0.2	0.1
50°-60°	0.1	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	275.3	99.0
0°-40°	277.7	99.9
0°-60°	278.0	100.0
0°-90°	278.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	278.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2710	
5°	2134	166
15°	276	93
25°	31	16
35°	3	2
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1302933
CATALOG NUMBER: P3RT02R159024DE010 E3CBUS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2709.5
2.5°	2558.8
5°	2133.6
7.5°	1558.0
10°	972.7
12.5°	526.0
15°	276.3
17.5°	153.1
20°	86.4
22.5°	50.4
25°	31.3
27.5°	19.1
30°	11.2
32.5°	5.1
35°	3.3
37.5°	1.9
40°	0.9
42.5°	0.5
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.5
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)