

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304853

Luminaire Tested: P3RT02R25B2750DE010 E3CBUS1MW_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1304853
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-87)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3RT02R25B2750DE010 E3CBUS1MW_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R25 optic, 2700K CCT AND, 90CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 277.0 lumens
Efficiency: N/A
Efficacy: 95.5 lumens/watt
Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.39
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 2.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1304853

CATALOG NUMBER: P3RT02R25B2750DE010 E3CBUS1MW_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1304853

CATALOG NUMBER: P3RT02R25B2750DE010 E3CBUS1MW_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	112	110	113	111	110	108	107	106	105		104	103	102		100
2	112	109	106	104	110	107	105	103	104	102	100		101	100	98		99
3	109	105	101	99	107	103	100	98	101	99	97		99	97	95		97
4	106	101	98	95	105	100	97	94	98	95	93		96	94	92		95
5	103	98	94	92	102	97	94	91	96	93	90		94	92	90		93
6	101	95	91	89	100	95	91	88	93	90	88		92	89	87		91
7	98	93	89	86	97	92	89	86	91	88	86		90	87	85		89
8	96	90	87	84	95	90	86	84	89	86	84		88	85	83		87
9	94	88	84	82	93	88	84	82	87	84	82		86	83	81		86
10	92	86	83	80	91	86	82	80	85	82	80		84	82	80		84

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	319558
5°	295993
10°	222886
15°	103587
20°	32600
25°	12606
30°	3646
35°	1178
40°	372
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1304853

CATALOG NUMBER: P3RT02R25B2750DE010 E3CBUS1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.5	42.4
10°-20°	129.5	46.8
20°-30°	26.6	9.6
30°-40°	3.2	1.2
40°-50°	0.2	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	273.6	98.8
0°-40°	276.8	99.9
0°-60°	277.0	100.0
0°-90°	277.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	277.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1457	
5°	1345	117
15°	456	129
25°	52	27
35°	4	3
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1304853

CATALOG NUMBER: P3RT02R25B2750DE010 E3CBUS1MW_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1457.3
2.5°	1429.2
5°	1344.7
7.5°	1203.3
10°	1001.0
12.5°	737.4
15°	456.3
17.5°	248.3
20°	139.7
22.5°	85.4
25°	52.1
27.5°	29.3
30°	14.4
32.5°	6.6
35°	4.4
37.5°	2.6
40°	1.3
42.5°	0.4
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)