

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1303137

Luminaire Tested: P3RT05R159027DE010 E3CBUS1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1303137
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-85)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3RT05R159027DE010 E3CBUS1MW
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 90CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 604.0 lumens
Efficiency: N/A
Efficacy: 83.9 lumens/watt
Spacing Criteria (0/90/45): 0.29 / 0.29 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1303137
CATALOG NUMBER: P3RT05R159027DE010 E3CBUS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1303137
 CATALOG NUMBER: P3RT05R159027DE010 E3CBUS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	100	100	100	98
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	98	98	98	96
3	110	106	103	101	109	105	102	100	103	101	99	101	99	97	98	97	96	96	96	96	95
4	108	103	100	98	106	102	100	97	101	98	96	99	97	95	97	96	94	97	96	94	93
5	106	101	98	95	104	100	97	95	99	96	94	97	95	93	96	94	93	96	94	93	92
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	95	93	91	90
7	102	97	93	91	101	96	93	91	95	92	90	94	92	90	93	91	90	93	91	90	89
8	100	95	92	89	99	94	91	89	94	91	89	93	90	89	92	90	88	92	90	88	88
9	98	93	90	88	97	93	90	88	92	89	88	91	89	87	91	89	87	91	89	87	86
10	97	92	89	87	96	91	88	86	91	88	86	90	88	86	90	87	86	90	87	86	85

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1290883
5°	1020358
10°	470577
15°	136300
20°	43777
25°	16428
30°	6153
35°	1901
40°	573
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 52.5°
 Luminance: 360 cd/sqm



TEST NUMBER: P1303137
 CATALOG NUMBER: P3RT05R159027DE010 E3CBUS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	360.0	59.6
10°-20°	202.6	33.5
20°-30°	35.5	5.9
30°-40°	5.3	0.9
40°-50°	0.4	0.1
50°-60°	0.2	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	598.1	99.0
0°-40°	603.4	99.9
0°-60°	604.0	100.0
0°-90°	604.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	604.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5887	
5°	4636	360
15°	600	203
25°	68	36
35°	7	5
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1303137
CATALOG NUMBER: P3RT05R159027DE010 E3CBUS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	5886.9
2.5°	5559.3
5°	4635.5
7.5°	3385.1
10°	2113.4
12.5°	1142.9
15°	600.4
17.5°	332.6
20°	187.6
22.5°	109.5
25°	67.9
27.5°	41.6
30°	24.3
32.5°	11.2
35°	7.1
37.5°	4.1
40°	2.0
42.5°	1.0
45°	0.0
47.5°	0.0
50°	0.0
52.5°	1.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)