

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304953

Luminaire Tested: P3RT05R65B2750DE010 E3CBUS1MW\_2700K

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1304953  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-94)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3RT05R65B2750DE010 E3CBUS1MW\_2700K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R65 optic, 2700K CCT AND, 90CRI , E3CBUS1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 502.0 lumens  
Efficiency: N/A  
Efficacy: 85.1 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.84  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1304953

CATALOG NUMBER: P3RT05R65B2750DE010 E3CBUS1MW\_2700K

### Luminous Intensity Polar Plot



TEST NUMBER: P1304953

CATALOG NUMBER: P3RT05R65B2750DE010 E3CBUS1MW\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |     |     | 0   |     |     |     | 0   |     |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 100 |
| 1   | 114 | 111 | 109 | 107 | 111 | 109 | 107 | 105 | 105 | 103 | 102 | 101 | 100 | 99  | 98  | 97  | 96  | 96  | 96  | 96  | 96  | 96  | 96  | 96  | 96  | 96  | 96  | 96  | 94  |
| 2   | 109 | 104 | 101 | 97  | 107 | 103 | 99  | 96  | 99  | 97  | 94  | 96  | 94  | 92  | 94  | 92  | 90  | 94  | 92  | 90  | 94  | 92  | 90  | 94  | 92  | 90  | 94  | 92  | 89  |
| 3   | 104 | 98  | 93  | 90  | 102 | 96  | 92  | 89  | 94  | 90  | 87  | 92  | 89  | 86  | 89  | 87  | 85  | 89  | 87  | 85  | 89  | 87  | 85  | 89  | 87  | 85  | 89  | 87  | 83  |
| 4   | 99  | 92  | 87  | 83  | 97  | 91  | 86  | 83  | 89  | 85  | 82  | 87  | 83  | 81  | 85  | 82  | 80  | 85  | 82  | 80  | 85  | 82  | 80  | 85  | 82  | 80  | 85  | 82  | 78  |
| 5   | 94  | 87  | 81  | 77  | 93  | 86  | 81  | 77  | 84  | 80  | 76  | 82  | 79  | 76  | 81  | 78  | 75  | 81  | 78  | 75  | 81  | 78  | 75  | 81  | 78  | 75  | 81  | 78  | 74  |
| 6   | 90  | 82  | 76  | 72  | 89  | 81  | 76  | 72  | 80  | 75  | 72  | 78  | 74  | 71  | 77  | 73  | 71  | 77  | 73  | 71  | 77  | 73  | 71  | 77  | 73  | 71  | 77  | 73  | 69  |
| 7   | 86  | 77  | 72  | 68  | 85  | 77  | 71  | 68  | 75  | 71  | 67  | 74  | 70  | 67  | 73  | 69  | 67  | 73  | 69  | 67  | 73  | 69  | 67  | 73  | 69  | 67  | 73  | 69  | 65  |
| 8   | 82  | 73  | 68  | 64  | 81  | 73  | 67  | 64  | 72  | 67  | 63  | 71  | 66  | 63  | 70  | 66  | 63  | 70  | 66  | 63  | 70  | 66  | 63  | 70  | 66  | 63  | 70  | 66  | 62  |
| 9   | 79  | 69  | 64  | 60  | 77  | 69  | 64  | 60  | 68  | 63  | 60  | 67  | 63  | 60  | 66  | 62  | 60  | 66  | 62  | 60  | 66  | 62  | 60  | 66  | 62  | 60  | 66  | 62  | 58  |
| 10  | 75  | 66  | 61  | 57  | 74  | 66  | 60  | 57  | 65  | 60  | 57  | 64  | 60  | 57  | 63  | 59  | 56  | 63  | 59  | 56  | 63  | 59  | 56  | 63  | 59  | 56  | 63  | 59  | 55  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 147115 |
| 5°  | 138961 |
| 10° | 134800 |
| 15° | 129240 |
| 20° | 117377 |
| 25° | 102103 |
| 30° | 70644  |
| 35° | 41037  |
| 40° | 10849  |
| 45° | 0      |
| 50° | 0      |
| 55° | 0      |
| 60° | 0      |
| 65° | 0      |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 0 cd/sqm

TEST NUMBER: P1304953

CATALOG NUMBER: P3RT05R65B2750DE010 E3CBUS1MW\_2700K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 59.6   | 11.9      |
| 10°-20°   | 158.1  | 31.5      |
| 20°-30°   | 185.7  | 37.0      |
| 30°-40°   | 94.1   | 18.7      |
| 40°-50°   | 4.5    | 0.9       |
| 50°-60°   | 0.0    | 0.0       |
| 60°-70°   | 0.0    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 403.4  | 80.4      |
| 0°-40°    | 497.5  | 99.1      |
| 0°-60°    | 502.0  | 100.0     |
| 0°-90°    | 502.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 502.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 671 |      |
| 5°  | 631 | 60   |
| 15° | 569 | 158  |
| 25° | 422 | 186  |
| 35° | 153 | 94   |
| 45° | 0   | 5    |
| 55° | 0   | 0    |
| 65° | 0   | 0    |
| 75° | 0   | 0    |
| 85° | 0   | 0    |
| 90° | 0   |      |

TEST NUMBER: P1304953

CATALOG NUMBER: P3RT05R65B2750DE010 E3CBUS1MW\_2700K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 670.9 |
| 2.5°  | 656.3 |
| 5°    | 631.3 |
| 7.5°  | 615.8 |
| 10°   | 605.4 |
| 12.5° | 591.7 |
| 15°   | 569.3 |
| 17.5° | 537.4 |
| 20°   | 503.0 |
| 22.5° | 467.6 |
| 25°   | 422.0 |
| 27.5° | 350.5 |
| 30°   | 279.0 |
| 32.5° | 217.0 |
| 35°   | 153.3 |
| 37.5° | 89.6  |
| 40°   | 37.9  |
| 42.5° | 6.0   |
| 45°   | 0.0   |
| 47.5° | 0.0   |
| 50°   | 0.0   |
| 52.5° | 0.0   |
| 55°   | 0.0   |
| 57.5° | 0.0   |
| 60°   | 0.0   |
| 62.5° | 0.0   |
| 65°   | 0.0   |
| 67.5° | 0.0   |
| 70°   | 0.0   |
| 72.5° | 0.0   |
| 75°   | 0.0   |
| 77.5° | 0.0   |
| 80°   | 0.0   |
| 82.5° | 0.0   |
| 85°   | 0.0   |
| 87.5° | 0.0   |
| 90°   | 0.0   |

(END OF REPORT)