

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1303378

Luminaire Tested: P3RT13R709030DE010 E3CBUS1MW

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1303378  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-95)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3RT13R709030DE010 E3CBUS1MW  
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 90CRI , E3CBUS1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1220.0 lumens  
Efficiency: N/A  
Efficacy: 83.6 lumens/watt  
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.99  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1303378  
CATALOG NUMBER: P3RT13R709030DE010 E3CBUS1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1303378  
 CATALOG NUMBER: P3RT13R709030DE010 E3CBUS1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	96	95	94	94	94	94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87	87	87	87
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81	81	81	81
4	98	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76	76	76	76
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71	71	71	71
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66
7	83	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	61	61	61	61
8	79	70	64	60	78	69	64	60	68	63	59	67	62	59	66	62	59	57	57	57	57
9	75	66	60	56	74	65	60	56	64	59	56	63	59	55	63	58	55	54	54	54	54
10	72	62	56	52	71	62	56	52	61	56	52	60	55	52	59	55	52	51	51	51	51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	296709
5°	282500
10°	270269
15°	257822
20°	238417
25°	216037
30°	186535
35°	167816
40°	65265
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 0 cd/sqm



TEST NUMBER: P1303378  
 CATALOG NUMBER: P3RT13R709030DE010 E3CBUS1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	120.3	9.9
10°-20°	317.3	26.0
20°-30°	405.9	33.3
30°-40°	350.4	28.7
40°-50°	26.1	2.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	843.5	69.1
0°-40°	1193.9	97.9
0°-60°	1220.0	100.0
0°-90°	1220.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1220.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1353	
5°	1283	120
15°	1136	317
25°	893	406
35°	627	350
45°	0	26
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1303378  
CATALOG NUMBER: P3RT13R709030DE010 E3CBUS1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1353.1
2.5°	1332.0
5°	1283.4
7.5°	1241.2
10°	1213.8
12.5°	1180.0
15°	1135.7
17.5°	1082.9
20°	1021.7
22.5°	954.1
25°	892.9
27.5°	814.8
30°	736.7
32.5°	705.0
35°	626.9
37.5°	456.0
40°	228.0
42.5°	29.6
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)