

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1305011

Luminaire Tested: P3RT09R60B2750DE010 E3CBUS1MW_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1305011
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-93)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3RT09R60B2750DE010 E3CBUS1MW_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R60 optic, 4000K CCT AND, 80CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 804.0 lumens
Efficiency: N/A
Efficacy: 61.4 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.84
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1305011

CATALOG NUMBER: P3RT09R60B2750DE010 E3CBUS1MW_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1305011

CATALOG NUMBER: P3RT09R60B2750DE010 E3CBUS1MW_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0				0				0
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100								
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96		94								
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90		89								
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89	87	85		83								
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85	82	79		78								
5	94	86	81	77	93	86	80	77	84	79	76		82	78	75		81	77	75		73								
6	90	82	76	72	89	81	76	72	79	75	71		78	74	71		77	73	70		69								
7	86	77	71	68	85	76	71	67	75	70	67		74	70	67		73	69	66		65								
8	82	73	67	63	81	72	67	63	71	67	63		70	66	63		69	66	63		61								
9	78	69	64	60	77	69	63	60	68	63	60		67	63	59		66	62	59		58								
10	75	66	60	57	74	65	60	56	64	60	56		64	59	56		63	59	56		55								

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	226451
5°	219744
10°	221728
15°	213917
20°	180966
25°	146960
30°	108650
35°	75329
40°	26965
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1305011

CATALOG NUMBER: P3RT09R60B2750DE010 E3CBUS1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.4	11.9
10°-20°	257.6	32.0
20°-30°	274.4	34.1
30°-40°	166.7	20.7
40°-50°	9.9	1.2
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	627.4	78.0
0°-40°	794.1	98.8
0°-60°	804.0	100.0
0°-90°	804.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	804.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1033	
5°	998	95
15°	942	258
25°	607	274
35°	281	167
45°	0	10
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1305011

CATALOG NUMBER: P3RT09R60B2750DE010 E3CBUS1MW_4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1032.7
2.5°	1017.4
5°	998.3
7.5°	993.2
10°	995.8
12.5°	984.3
15°	942.3
17.5°	868.4
20°	775.5
22.5°	686.3
25°	607.4
27.5°	515.7
30°	429.1
32.5°	361.6
35°	281.4
37.5°	183.4
40°	94.2
42.5°	7.6
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)