

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1303569

Luminaire Tested: P3RT17R309035DE010 E3CBUS1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1303569
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-88)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3RT17R309035DE010 E3CBUS1MW
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 90CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1842.0 lumens
Efficiency: N/A
Efficacy: 86.9 lumens/watt
Spacing Criteria (0/90/45): 0.5 / 0.5 / 0.45
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1303569

CATALOG NUMBER: P3RT17R309035DE010 E3CBUS1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1303569

CATALOG NUMBER: P3RT17R309035DE010 E3CBUS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	115	113	111	110	113	111	109	108	107	106	105	103	103	102	100	99	99	97	96	96
2	112	108	105	103	110	107	104	102	104	101	100	101	99	98	98	97	96	94	93	93
3	108	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	91	91
4	105	100	97	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89	88	88
5	102	97	93	90	101	96	93	90	95	91	89	93	90	88	92	89	88	87	86	86
6	100	94	90	87	99	93	90	87	92	89	86	91	88	86	90	87	85	84	83	83
7	97	91	87	84	96	91	87	84	90	86	84	89	86	83	88	85	83	82	81	81
8	95	89	85	82	94	88	84	82	87	84	82	86	83	81	86	83	81	80	79	79
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	77	77
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76	75	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1652280
5°	1605389
10°	1358737
15°	818370
20°	294726
25°	82843
30°	21851
35°	8459
40°	3292
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1303569

CATALOG NUMBER: P3RT17R309035DE010 E3CBUS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	659.9	35.8
10°-20°	959.3	52.1
20°-30°	198.1	10.8
30°-40°	23.1	1.3
40°-50°	1.6	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1817.3	98.7
0°-40°	1840.4	99.9
0°-60°	1842.0	100.0
0°-90°	1842.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1842.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7535	
5°	7293	660
15°	3605	959
25°	342	198
35°	32	23
45°	0	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1303569

CATALOG NUMBER: P3RT17R309035DE010 E3CBUS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	7535.0
2.5°	7474.6
5°	7293.3
7.5°	6893.4
10°	6102.2
12.5°	4965.8
15°	3604.9
17.5°	2307.4
20°	1263.0
22.5°	632.9
25°	342.4
27.5°	187.0
30°	86.3
32.5°	51.8
35°	31.6
37.5°	20.1
40°	11.5
42.5°	2.9
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)