

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304227

Luminaire Tested: P3RT17R509730DE010 E3CBUS1MW

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1304227  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-91)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3RT17R509730DE010 E3CBUS1MW  
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 97CRI , E3CBUS1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1675.0 lumens  
Efficiency: N/A  
Efficacy: 79.0 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 0.71 / 0.72  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1304227

CATALOG NUMBER: P3RT17R509730DE010 E3CBUS1MW

### Luminous Intensity Polar Plot



TEST NUMBER: P1304227

CATALOG NUMBER: P3RT17R509730DE010 E3CBUS1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 99 | 99 |
| 1   | 114 | 112 | 110 | 108 | 112 | 110 | 108 | 106 | 106 | 104 | 103 | 102 | 101 | 100 | 99  | 98  | 97  | 95  | 94 | 93 |
| 2   | 110 | 105 | 102 | 99  | 108 | 104 | 101 | 98  | 101 | 98  | 96  | 98  | 96  | 94  | 95  | 93  | 92  | 90  | 89 | 88 |
| 3   | 105 | 100 | 95  | 92  | 103 | 98  | 94  | 91  | 96  | 93  | 90  | 93  | 91  | 89  | 91  | 89  | 87  | 86  | 85 | 84 |
| 4   | 101 | 95  | 90  | 86  | 99  | 93  | 89  | 86  | 91  | 88  | 85  | 89  | 86  | 84  | 88  | 85  | 83  | 82  | 81 | 80 |
| 5   | 97  | 90  | 85  | 81  | 95  | 89  | 84  | 81  | 87  | 83  | 80  | 86  | 82  | 79  | 84  | 81  | 79  | 78  | 77 | 76 |
| 6   | 93  | 85  | 80  | 77  | 92  | 85  | 80  | 76  | 83  | 79  | 76  | 82  | 78  | 75  | 81  | 78  | 75  | 74  | 73 | 72 |
| 7   | 89  | 81  | 76  | 73  | 88  | 81  | 76  | 73  | 80  | 75  | 72  | 79  | 75  | 72  | 77  | 74  | 72  | 70  | 69 | 68 |
| 8   | 86  | 78  | 73  | 69  | 85  | 77  | 72  | 69  | 76  | 72  | 69  | 75  | 71  | 69  | 74  | 71  | 68  | 67  | 66 | 65 |
| 9   | 83  | 74  | 69  | 66  | 82  | 74  | 69  | 66  | 73  | 69  | 66  | 72  | 68  | 65  | 71  | 68  | 65  | 64  | 63 | 62 |
| 10  | 79  | 71  | 66  | 63  | 79  | 71  | 66  | 63  | 70  | 66  | 63  | 69  | 65  | 63  | 69  | 65  | 62  | 61  | 60 | 59 |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 675319 |
| 5°  | 659144 |
| 10° | 622678 |
| 15° | 547245 |
| 20° | 411659 |
| 25° | 304348 |
| 30° | 184636 |
| 35° | 61034  |
| 40° | 10763  |
| 45° | 0      |
| 50° | 0      |
| 55° | 0      |
| 60° | 0      |
| 65° | 0      |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 0 cd/sqm

TEST NUMBER: P1304227

CATALOG NUMBER: P3RT17R509730DE010 E3CBUS1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 279.6  | 16.7      |
| 10°-20°   | 655.6  | 39.1      |
| 20°-30°   | 562.2  | 33.6      |
| 30°-40°   | 173.4  | 10.3      |
| 40°-50°   | 4.3    | 0.3       |
| 50°-60°   | 0.0    | 0.0       |
| 60°-70°   | 0.0    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 1497.3 | 89.4      |
| 0°-40°    | 1670.7 | 99.7      |
| 0°-60°    | 1675.0 | 100.0     |
| 0°-90°    | 1675.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1675.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 3080 |      |
| 5°  | 2994 | 280  |
| 15° | 2411 | 656  |
| 25° | 1258 | 562  |
| 35° | 228  | 173  |
| 45° | 0    | 4    |
| 55° | 0    | 0    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |

TEST NUMBER: P1304227

CATALOG NUMBER: P3RT17R509730DE010 E3CBUS1MW

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 3079.7 |
| 2.5°  | 3057.1 |
| 5°    | 2994.5 |
| 7.5°  | 2906.8 |
| 10°   | 2796.5 |
| 12.5° | 2621.1 |
| 15°   | 2410.6 |
| 17.5° | 2142.5 |
| 20°   | 1764.1 |
| 22.5° | 1443.4 |
| 25°   | 1257.9 |
| 27.5° | 1022.4 |
| 30°   | 729.2  |
| 32.5° | 443.5  |
| 35°   | 228.0  |
| 37.5° | 102.7  |
| 40°   | 37.6   |
| 42.5° | 5.0    |
| 45°   | 0.0    |
| 47.5° | 0.0    |
| 50°   | 0.0    |
| 52.5° | 0.0    |
| 55°   | 0.0    |
| 57.5° | 0.0    |
| 60°   | 0.0    |
| 62.5° | 0.0    |
| 65°   | 0.0    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |

(END OF REPORT)