

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304395

Luminaire Tested: P3RT17R159735DE010 E3CBUS1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1304395
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-85)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3RT17R159735DE010 E3CBUS1MW
Description: 3in Adjustable LED luminaire with, R15 optic, 3500K CCT AND, 97CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1551.0 lumens
Efficiency: N/A
Efficacy: 73.2 lumens/watt
Spacing Criteria (0/90/45): 0.29 / 0.29 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1304395

CATALOG NUMBER: P3RT17R159735DE010 E3CBUS1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1304395

CATALOG NUMBER: P3RT17R159735DE010 E3CBUS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	100	100	98
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	99	98	98	98	96
3	110	106	103	101	109	105	102	100	103	101	99	101	99	97	98	97	96	96	96	95
4	108	103	100	98	106	102	100	97	101	98	96	99	97	95	97	96	94	94	94	93
5	106	101	98	95	104	100	97	95	99	96	94	97	95	93	96	94	93	93	93	92
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	91	91	90
7	102	97	93	91	101	96	93	91	95	92	90	94	92	90	93	91	90	90	90	89
8	100	95	92	89	99	94	91	89	94	91	89	93	90	89	92	90	88	88	88	88
9	98	93	90	88	97	93	90	88	92	89	88	91	89	87	91	89	87	87	87	86
10	97	92	89	87	96	91	88	86	91	88	86	90	88	86	90	87	86	86	86	85

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3314844
5°	2620156
10°	1208394
15°	349968
20°	112430
25°	42220
30°	15825
35°	4872
40°	1489
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 52.5°

Luminance: 937 cd/sqm

TEST NUMBER: P1304395

CATALOG NUMBER: P3RT17R159735DE010 E3CBUS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	924.3	59.6
10°-20°	520.2	33.5
20°-30°	91.3	5.9
30°-40°	13.7	0.9
40°-50°	1.0	0.1
50°-60°	0.6	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1535.8	99.0
0°-40°	1549.5	99.9
0°-60°	1551.0	100.0
0°-90°	1551.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1551.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15117	
5°	11903	924
15°	1542	520
25°	174	91
35°	18	14
45°	0	1
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1304395

CATALOG NUMBER: P3RT17R159735DE010 E3CBUS1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	15116.9
2.5°	14275.7
5°	11903.4
7.5°	8692.5
10°	5427.0
12.5°	2934.8
15°	1541.6
17.5°	854.1
20°	481.8
22.5°	281.2
25°	174.5
27.5°	106.8
30°	62.5
32.5°	28.6
35°	18.2
37.5°	10.4
40°	5.2
42.5°	2.6
45°	0.0
47.5°	0.0
50°	0.0
52.5°	2.6
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)