

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304568

Luminaire Tested: P3RT13R709740DE010 E3CBUS1MW

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1304568  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-95)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3RT13R709740DE010 E3CBUS1MW  
Description: 3in Adjustable LED luminaire with, R70 optic, 4000K CCT AND, 97CRI , E3CBUS1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1182.0 lumens  
Efficiency: N/A  
Efficacy: 81.0 lumens/watt  
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.99  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1304568  
CATALOG NUMBER: P3RT13R709740DE010 E3CBUS1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1304568  
 CATALOG NUMBER: P3RT13R709740DE010 E3CBUS1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	96	95	94				94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87				87
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81				81
4	98	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76				76
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71				71
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66				66
7	83	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	61				61
8	79	70	64	60	78	69	64	60	68	63	59	67	62	59	66	62	59	57				57
9	75	66	60	56	74	65	60	56	64	59	56	63	59	55	63	58	55	54				54
10	72	62	56	52	71	62	56	52	61	56	52	60	55	52	59	55	52	51				51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	287455
5°	273695
10°	261852
15°	249786
20°	230973
25°	209310
30°	180737
35°	162596
40°	63233
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 0 cd/sqm



TEST NUMBER: P1304568  
 CATALOG NUMBER: P3RT13R709740DE010 E3CBUS1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	116.6	9.9
10°-20°	307.4	26.0
20°-30°	393.3	33.3
30°-40°	339.5	28.7
40°-50°	25.3	2.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	817.3	69.1
0°-40°	1156.8	97.9
0°-60°	1182.0	100.0
0°-90°	1182.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1182.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1311	
5°	1243	117
15°	1100	307
25°	865	393
35°	607	339
45°	0	25
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1304568  
CATALOG NUMBER: P3RT13R709740DE010 E3CBUS1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1310.9
2.5°	1290.5
5°	1243.4
7.5°	1202.5
10°	1176.0
12.5°	1143.2
15°	1100.3
17.5°	1049.2
20°	989.8
22.5°	924.4
25°	865.1
27.5°	789.4
30°	713.8
32.5°	683.1
35°	607.4
37.5°	441.8
40°	220.9
42.5°	28.6
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)