

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304504

Luminaire Tested: P3RT05R359740DE010 E3CBUS1MW

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1304504  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-89)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3RT05R359740DE010 E3CBUS1MW  
Description: 3in Adjustable LED luminaire with, R35 optic, 4000K CCT AND, 97CRI , E3CBUS1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 677.0 lumens  
Efficiency: N/A  
Efficacy: 94.0 lumens/watt  
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.5  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1304504  
CATALOG NUMBER: P3RT05R359740DE010 E3CBUS1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1304504  
 CATALOG NUMBER: P3RT05R359740DE010 E3CBUS1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98
1	115	113	111	109	113	111	109	108	107	105	104	103	102	101	100	99	98	97	96	95
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	94	93	92
3	108	103	99	97	106	102	98	96	99	97	94	97	95	93	95	93	92	91	90	89
4	104	99	95	92	103	98	94	92	96	93	90	94	92	89	92	90	89	88	87	86
5	101	95	91	88	100	94	91	88	93	90	87	91	89	86	90	88	86	85	84	83
6	98	92	88	85	97	91	87	85	90	87	84	89	86	83	88	85	83	82	81	80
7	95	89	85	82	94	88	84	82	87	84	81	86	83	81	85	83	80	79	78	77
8	93	86	82	79	92	86	82	79	85	81	79	84	81	78	83	80	78	77	76	75
9	90	83	79	77	89	83	79	76	82	79	76	82	78	76	81	78	76	75	74	73
10	88	81	77	74	87	81	77	74	80	76	74	79	76	74	79	76	74	73	72	71

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	495947
5°	481157
10°	429050
15°	303089
20°	146196
25°	47374
30°	13319
35°	5354
40°	1517
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 0 cd/sqm



TEST NUMBER: P1304504  
 CATALOG NUMBER: P3RT05R359740DE010 E3CBUS1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	200.7	29.7
10°-20°	352.9	52.1
20°-30°	108.4	16.0
30°-40°	14.1	2.1
40°-50°	0.9	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	662.0	97.8
0°-40°	676.1	99.9
0°-60°	677.0	100.0
0°-90°	677.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	677.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2262	
5°	2186	201
15°	1335	353
25°	196	108
35°	20	14
45°	0	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1304504  
CATALOG NUMBER: P3RT05R359740DE010 E3CBUS1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2261.7
2.5°	2243.8
5°	2185.9
7.5°	2090.1
10°	1926.9
12.5°	1672.1
15°	1335.1
17.5°	968.7
20°	626.5
22.5°	363.3
25°	195.8
27.5°	103.2
30°	52.6
32.5°	31.6
35°	20.0
37.5°	12.6
40°	5.3
42.5°	2.1
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)