

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1245547

Luminaire Tested: P3AS02R109024DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245547
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R109024DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R10 optic, 2400K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 156.0 lumens
Efficiency: N/A
Efficacy: 41.1 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1245547

CATALOG NUMBER: P3AS02R109024DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1245547

CATALOG NUMBER: P3AS02R109024DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	73	68	87	79	73	68	77	72	67		75	70	67		73
6	84	74	68	63	83	73	67	63	72	66	62		70	66	62		69
7	80	69	63	58	78	69	63	58	67	62	58		66	61	57		65
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	52	47	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	39339
5°	38279
10°	34980
15°	30647
20°	26276
25°	21945
30°	17572
35°	13170
40°	9561
45°	6264
50°	3923
55°	2638
60°	2324
65°	2179
70°	2052
75°	1864
80°	1768
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6264 cd/sqm

TEST NUMBER: P1245547

CATALOG NUMBER: P3AS02R109024DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.0	10.3
10°-20°	37.6	24.1
20°-30°	41.4	26.6
30°-40°	31.0	19.9
40°-50°	16.1	10.3
50°-60°	6.7	4.3
60°-70°	4.1	2.7
70°-80°	2.3	1.5
80°-90°	0.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	95.1	60.9
0°-40°	126.1	80.8
0°-60°	148.9	95.4
0°-90°	156.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	156.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	179	
5°	174	16
15°	135	38
25°	91	41
35°	49	31
45°	20	16
55°	7	7
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1245547

CATALOG NUMBER: P3AS02R109024DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	179.4
1°	179.6
2°	179.1
3°	177.9
4°	176.1
5°	173.9
6°	171.1
7°	168.2
8°	164.6
9°	160.9
10°	157.1
12.5°	146.2
15°	135.0
17.5°	123.7
20°	112.6
22.5°	101.4
25°	90.7
27.5°	80.0
30°	69.4
32.5°	58.9
35°	49.2
37.5°	40.9
40°	33.4
42.5°	26.5
45°	20.2
47.5°	15.2
50°	11.5
52.5°	8.5
55°	6.9
57.5°	6.1
60°	5.3
62.5°	4.7
65°	4.2
67.5°	3.6
70°	3.2
72.5°	2.6
75°	2.2
77.5°	1.8
80°	1.4
82.5°	1.0
85°	0.6
87.5°	0.2
90°	0.0

(END OF REPORT)