

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1245619

Luminaire Tested: P3AS02R159024DE010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245619
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-5)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R159024DE010 E3PHLP1MW
Description: 3in Adjustable LED luminaire with, R15 optic, 2400K CCT AND, 90CRI , E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 100.0 lumens
Efficiency: N/A
Efficacy: 27.8 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1245619

CATALOG NUMBER: P3AS02R159024DE010 E3PHLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1245619

CATALOG NUMBER: P3AS02R159024DE010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90		
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81		
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	74		
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68		
5	88	78	72	67	86	77	71	67	76	70	66	74	69	65	72	68	65	63		
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59		
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55		
8	75	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52		
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49		
10	69	59	52	48	68	58	52	48	57	52	48	56	51	48	56	51	48	46		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	37431
5°	34360
10°	27388
15°	20454
20°	15541
25°	11759
30°	8710
35°	6210
40°	4265
45°	2977
50°	2524
55°	2485
60°	2588
65°	2750
70°	2757
75°	2881
80°	3157
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 82.5°
Luminance: 3696 cd/sqm

TEST NUMBER: P1245619

CATALOG NUMBER: P3AS02R159024DE010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	13.8	13.8
10°-20°	25.3	25.3
20°-30°	22.4	22.4
30°-40°	14.7	14.7
40°-50°	7.9	7.9
50°-60°	5.9	5.9
60°-70°	5.1	5.1
70°-80°	3.5	3.5
80°-90°	1.4	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	61.5	61.5
0°-40°	76.2	76.2
0°-60°	89.9	90.0
0°-90°	100.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	100.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	171	
5°	156	14
15°	90	25
25°	49	22
35°	23	15
45°	10	8
55°	6	6
65°	5	5
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P1245619

CATALOG NUMBER: P3AS02R159024DE010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	170.7
2.5°	166.7
5°	156.1
7.5°	140.6
10°	123.0
12.5°	105.9
15°	90.1
17.5°	77.4
20°	66.6
22.5°	57.0
25°	48.6
27.5°	41.2
30°	34.4
32.5°	28.5
35°	23.2
37.5°	18.6
40°	14.9
42.5°	11.8
45°	9.6
47.5°	8.4
50°	7.4
52.5°	7.1
55°	6.5
57.5°	6.2
60°	5.9
62.5°	5.6
65°	5.3
67.5°	4.6
70°	4.3
72.5°	3.7
75°	3.4
77.5°	2.8
80°	2.5
82.5°	2.2
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)