

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1245653

Luminaire Tested: P3AS02R259024DE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245653
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259024DE010 E3D1LI
Description: 3in Adjustable LED luminaire with, R25 optic, 2400K CCT AND, 90CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 290.0 lumens
Efficiency: N/A
Efficacy: 80.6 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1245653

CATALOG NUMBER: P3AS02R259024DE010 E3D1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1245653

CATALOG NUMBER: P3AS02R259024DE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	115	113	111	110	113	111	110	108	107	106	105		104	103	102		97
2	112	108	106	103	110	107	104	102	104	102	100		101	99	98		94
3	109	104	101	98	107	103	100	97	100	98	96		98	96	94		92
4	106	101	97	94	104	100	96	94	98	95	92		96	93	91		89
5	103	97	93	91	101	96	93	90	95	92	90		93	91	89		87
6	100	94	90	88	99	94	90	87	92	89	87		91	88	86		85
7	98	92	88	85	97	91	87	85	90	87	84		89	86	84		83
8	95	89	85	83	94	89	85	83	88	85	82		87	84	82		81
9	93	87	83	81	92	86	83	80	86	83	80		85	82	80		79
10	91	85	81	79	90	84	81	79	84	81	78		83	80	78		77

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	317606
5°	294210
10°	227629
15°	108718
20°	35843
25°	15122
30°	5849
35°	2543
40°	830
45°	403
50°	136
55°	76
60°	44
65°	52
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 403 cd/sqm

TEST NUMBER: P1245653

CATALOG NUMBER: P3AS02R259024DE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.5	40.5
10°-20°	133.6	46.1
20°-30°	31.1	10.7
30°-40°	6.5	2.2
40°-50°	1.0	0.4
50°-60°	0.2	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	282.2	97.3
0°-40°	288.7	99.6
0°-60°	289.9	100.0
0°-90°	290.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	290.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1448	
5°	1337	117
15°	479	134
25°	62	31
35°	10	7
45°	1	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1245653

CATALOG NUMBER: P3AS02R259024DE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1448.4
1°	1445.4
2°	1430.4
3°	1409.3
4°	1377.0
5°	1336.6
6°	1284.8
7°	1230.5
8°	1169.6
9°	1101.0
10°	1022.3
11°	931.2
12°	826.6
13°	711.9
14°	592.1
15°	478.9
16°	378.8
17°	295.1
18°	232.2
19°	185.7
20°	153.6
21°	128.4
22°	107.8
23°	90.0
24°	75.3
25°	62.5
27.5°	37.0
30°	23.1
32.5°	14.8
35°	9.5
37.5°	5.7
40°	2.9
42.5°	1.9
45°	1.3
47.5°	0.7
50°	0.4
52.5°	0.2
55°	0.2
57.5°	0.1
60°	0.1
62.5°	0.1
65°	0.1
67.5°	0.1
70°	0.0
72.5°	0.0



TEST NUMBER: P1245653

CATALOG NUMBER: P3AS02R259024DE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)