

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1245657

Luminaire Tested: P3AS02R259024DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245657
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259024DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 2400K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 110.0 lumens
Efficiency: N/A
Efficacy: 30.5 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1245657

CATALOG NUMBER: P3AS02R259024DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1245657

CATALOG NUMBER: P3AS02R259024DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	105	102	99	108	104	101	98	101	98	96		98	96	94		95
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91
4	101	95	90	87	99	94	89	86	92	88	85		90	87	84		88
5	97	90	85	82	96	89	85	82	88	84	81		86	83	80		85
6	94	86	81	78	92	86	81	78	84	80	77		83	79	77		82
7	90	83	78	74	89	82	77	74	81	77	74		80	76	73		79
8	87	79	74	71	86	79	74	71	78	74	71		77	73	70		76
9	84	76	71	68	83	76	71	68	75	71	68		74	70	68		73
10	81	73	69	65	80	73	68	65	72	68	65		72	68	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	70565
5°	65837
10°	52727
15°	35800
20°	21655
25°	12678
30°	7216
35°	3962
40°	2118
45°	1116
50°	648
55°	497
60°	395
65°	415
70°	385
75°	339
80°	253
85°	252

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1116 cd/sqm

TEST NUMBER: P1245657

CATALOG NUMBER: P3AS02R259024DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.5	24.1
10°-20°	43.4	39.4
20°-30°	24.8	22.5
30°-40°	9.8	8.9
40°-50°	3.0	2.7
50°-60°	1.2	1.1
60°-70°	0.8	0.7
70°-80°	0.4	0.4
80°-90°	0.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	94.7	86.1
0°-40°	104.4	95.0
0°-60°	108.6	98.8
0°-90°	110.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	110.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	322	
5°	299	27
15°	158	43
25°	52	25
35°	15	10
45°	4	3
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1245657

CATALOG NUMBER: P3AS02R259024DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	321.8
1°	321.2
2°	318.5
3°	313.9
4°	307.5
5°	299.1
6°	289.2
7°	278.1
8°	265.1
9°	251.9
10°	236.8
11°	222.0
12°	205.7
13°	189.6
14°	173.1
15°	157.7
17.5°	122.3
20°	92.8
22.5°	69.7
25°	52.4
27.5°	38.8
30°	28.5
32.5°	20.6
35°	14.8
37.5°	10.5
40°	7.4
42.5°	5.0
45°	3.6
47.5°	2.5
50°	1.9
52.5°	1.5
55°	1.3
57.5°	1.2
60°	0.9
62.5°	0.8
65°	0.8
67.5°	0.7
70°	0.6
72.5°	0.5
75°	0.4
77.5°	0.3
80°	0.2
82.5°	0.2
85°	0.1
87.5°	0.1



TEST NUMBER: P1245657

CATALOG NUMBER: P3AS02R259024DE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)