

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1245747

Luminaire Tested: P3AS02R409024DE010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245747
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R409024DE010 E3D1WH
Description: 3in Adjustable LED luminaire with, R40 optic, 2400K CCT AND, 90CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 301.0 lumens
Efficiency: N/A
Efficacy: 83.6 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1245747
CATALOG NUMBER: P3AS02R409024DE010 E3D1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1245747
 CATALOG NUMBER: P3AS02R409024DE010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	96	96	96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92	92	92
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	93	91	90	88	88	88
4	103	97	93	90	101	96	92	89	94	91	88	92	89	87	90	88	86	85	85	85
5	99	93	89	85	98	92	88	85	91	87	84	89	86	84	88	85	83	82	82	82
6	96	89	85	81	95	89	84	81	87	83	81	86	83	80	85	82	80	79	79	79
7	93	86	81	78	92	85	81	78	84	80	78	83	80	77	82	79	77	76	76	76
8	90	83	78	75	89	82	78	75	81	77	75	80	77	74	79	76	74	73	73	73
9	87	80	75	72	86	79	75	72	78	75	72	78	74	72	77	74	71	70	70	70
10	84	77	72	70	83	77	72	69	76	72	69	75	72	69	75	71	69	68	68	68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	153431
5°	152322
10°	148338
15°	132509
20°	87858
25°	32905
30°	8811
35°	3453
40°	1231
45°	589
50°	171
55°	76
60°	44
65°	52
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 589 cd/sqm



TEST NUMBER: P1245747
 CATALOG NUMBER: P3AS02R409024DE010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.3	21.7
10°-20°	154.7	51.4
20°-30°	70.1	23.3
30°-40°	9.1	3.0
40°-50°	1.6	0.5
50°-60°	0.2	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	290.1	96.4
0°-40°	299.2	99.4
0°-60°	300.9	100.0
0°-90°	301.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	301.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	700	
5°	692	65
15°	584	155
25°	136	70
35°	13	9
45°	2	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1245747
CATALOG NUMBER: P3AS02R409024DE010 E3D1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	699.7
1°	699.3
2°	698.2
3°	696.6
4°	694.6
5°	692.0
6°	688.9
7°	685.1
8°	680.5
9°	674.2
10°	666.2
11°	656.8
12°	644.3
13°	628.8
14°	608.5
15°	583.7
16°	551.9
17°	515.8
18°	472.4
19°	426.6
20°	376.5
21°	326.4
22°	277.1
23°	228.0
24°	179.8
25°	136.0
26°	100.7
27°	73.8
28°	55.4
29°	43.1
30°	34.8
31°	28.8
32°	24.0
32.5°	21.9
33°	19.8
34°	16.1
35°	12.9
36°	10.1
37°	8.0
37.5°	7.2
38°	6.3
39°	5.3
40°	4.3
42.5°	2.8
45°	1.9



TEST NUMBER: P1245747
CATALOG NUMBER: P3AS02R409024DE010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	1.2
50°	0.5
52.5°	0.2
55°	0.2
57.5°	0.1
60°	0.1
62.5°	0.1
65°	0.1
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)