

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1245771

Luminaire Tested: P3AS02R459024DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245771
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-28)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R459024DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R45 optic, 2400K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 287.9 lumens
Efficiency: N/A
Efficacy: 80.0 lumens/watt
Spacing Criteria (0/90/45): 0.72 / 0.72 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1245771
CATALOG NUMBER: P3AS02R459024DE010 E3CD1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1245771

CATALOG NUMBER: P3AS02R459024DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91	91	91	91
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	87	87	87	87
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	89	86	84	83	83	83	83
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79	79	79	79
6	94	87	82	78	93	86	81	78	85	81	77	83	80	77	82	79	77	75	75	75	75
7	90	83	78	75	89	82	78	74	81	77	74	80	76	74	79	76	73	72	72	72	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66	66	66	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	64	64	64	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	124858
5°	125533
10°	121663
15°	101953
20°	77940
25°	47446
30°	19750
35°	6318
40°	1975
45°	403
50°	307
55°	344
60°	263
65°	311
70°	256
75°	339
80°	253
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 403 cd/sqm



TEST NUMBER: P1245771
 CATALOG NUMBER: P3AS02R459024DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.8	18.7
10°-20°	123.4	42.9
20°-30°	88.9	30.9
30°-40°	18.5	6.4
40°-50°	1.7	0.6
50°-60°	0.7	0.2
60°-70°	0.5	0.2
70°-80°	0.3	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	266.1	92.4
0°-40°	284.6	98.8
0°-60°	287.0	99.7
0°-90°	287.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	287.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	569	
5°	570	54
15°	449	123
25°	196	89
35°	24	18
45°	1	2
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1245771
CATALOG NUMBER: P3AS02R459024DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	569.4
2.5°	569.6
5°	570.3
7.5°	566.2
10°	546.4
12.5°	505.2
15°	449.1
17.5°	391.8
20°	334.0
22.5°	267.6
25°	196.1
27.5°	129.3
30°	78.0
32.5°	43.6
35°	23.6
37.5°	13.3
40°	6.9
42.5°	3.0
45°	1.3
47.5°	0.9
50°	0.9
52.5°	0.9
55°	0.9
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.6
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.2
80°	0.2
82.5°	0.2
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)