

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1245806

Luminaire Tested: P3AS02R509024DE010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245806
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R509024DE010 E3DL1MW
Description: 3in Adjustable LED luminaire with, R50 optic, 2400K CCT AND, 90CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 242.0 lumens
Efficiency: N/A
Efficacy: 67.2 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1245806

CATALOG NUMBER: P3AS02R509024DE010 E3DL1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1245806

CATALOG NUMBER: P3AS02R509024DE010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94		
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87		
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82		
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	80	78	76		
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72		
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	75	72	69	68		
7	85	76	70	66	84	75	70	66	74	69	66	73	69	65	72	68	65	64		
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61	60		
9	78	68	63	59	76	68	62	59	67	62	59	66	62	58	65	61	58	57		
10	74	65	59	56	73	65	59	56	64	59	55	63	59	55	62	58	55	54		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	77055
5°	75501
10°	70718
15°	63315
20°	53275
25°	40648
30°	26434
35°	15660
40°	9046
45°	4528
50°	1672
55°	1300
60°	1228
65°	1141
70°	1090
75°	1101
80°	1137
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4528 cd/sqm

TEST NUMBER: P1245806

CATALOG NUMBER: P3AS02R509024DE010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.9	13.2
10°-20°	77.1	31.9
20°-30°	75.6	31.3
30°-40°	38.1	15.7
40°-50°	12.0	5.0
50°-60°	3.1	1.3
60°-70°	2.2	0.9
70°-80°	1.4	0.6
80°-90°	0.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	184.7	76.3
0°-40°	222.8	92.1
0°-60°	237.9	98.3
0°-90°	242.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	242.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	351	
5°	343	32
15°	279	77
25°	168	76
35°	58	38
45°	15	12
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1245806

CATALOG NUMBER: P3AS02R509024DE010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	351.4
2.5°	349.2
5°	343.0
7.5°	331.8
10°	317.6
12.5°	299.3
15°	278.9
17.5°	255.2
20°	228.3
22.5°	199.2
25°	168.0
27.5°	134.9
30°	104.4
32.5°	78.5
35°	58.5
37.5°	43.2
40°	31.6
42.5°	22.4
45°	14.6
47.5°	8.4
50°	4.9
52.5°	3.7
55°	3.4
57.5°	3.0
60°	2.8
62.5°	2.6
65°	2.2
67.5°	1.9
70°	1.7
72.5°	1.5
75°	1.3
77.5°	1.1
80°	0.9
82.5°	0.6
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)