

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1245830

Luminaire Tested: P3AS02R559024DE010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245830
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R559024DE010 E3D1WH
Description: 3in Adjustable LED luminaire with, R55 optic, 2400K CCT AND, 90CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 277.0 lumens
Efficiency: N/A
Efficacy: 76.9 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1245830

CATALOG NUMBER: P3AS02R559024DE010 E3D1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1245830

CATALOG NUMBER: P3AS02R559024DE010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94	92	91	89
3	104	98	94	90	102	97	93	90	95	91	88		92	89	87		90	88	86	84
4	100	93	88	84	98	92	87	84	90	86	83		88	84	82		86	83	81	79
5	95	88	83	79	94	87	82	78	85	81	78		84	80	77		82	79	76	75
6	91	83	78	74	90	82	77	74	81	76	73		80	76	73		78	75	72	71
7	87	79	73	70	86	78	73	69	77	72	69		76	72	69		75	71	68	67
8	83	75	69	66	82	74	69	66	73	69	65		72	68	65		71	68	65	63
9	80	71	66	62	79	71	66	62	70	65	62		69	65	62		68	64	61	60
10	77	68	62	59	76	67	62	59	67	62	59		66	62	59		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	80323
5°	77482
10°	80248
15°	79115
20°	73226
25°	59229
30°	35499
35°	12019
40°	3321
45°	1458
50°	443
55°	76
60°	44
65°	52
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1458 cd/sqm

TEST NUMBER: P1245830

CATALOG NUMBER: P3AS02R559024DE010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.1	12.3
10°-20°	97.0	35.0
20°-30°	107.9	38.9
30°-40°	33.6	12.1
40°-50°	4.0	1.5
50°-60°	0.3	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	239.0	86.3
0°-40°	272.5	98.4
0°-60°	276.9	100.0
0°-90°	277.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	277.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	366	
5°	352	34
15°	348	97
25°	245	108
35°	45	34
45°	5	4
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1245830

CATALOG NUMBER: P3AS02R559024DE010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	366.3
1°	365.0
2°	361.4
3°	357.0
4°	353.0
5°	352.0
6°	353.1
7°	355.3
8°	357.8
9°	359.8
10°	360.4
11°	360.0
12°	358.3
13°	355.7
14°	352.6
15°	348.5
16°	343.8
17°	337.8
18°	331.1
19°	323.0
20°	313.8
21°	303.4
22°	291.1
23°	277.5
24°	261.9
25°	244.8
26°	225.9
27°	205.9
28°	184.6
29°	162.6
30°	140.2
31°	117.7
32°	95.7
32.5°	85.9
33°	75.8
34°	58.6
35°	44.9
36°	34.2
37°	25.4
37.5°	21.7
38°	18.8
39°	14.3
40°	11.6
42.5°	7.4
45°	4.7



TEST NUMBER: P1245830

CATALOG NUMBER: P3AS02R559024DE010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	2.8
50°	1.3
52.5°	0.4
55°	0.2
57.5°	0.1
60°	0.1
62.5°	0.1
65°	0.1
67.5°	0.1
70°	0.1
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)