

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1245840

Luminaire Tested: P3AS02R559024DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245840
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R559024DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R55 optic, 2400K CCT AND, 90CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 182.0 lumens
Efficiency: N/A
Efficacy: 50.5 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1245840

CATALOG NUMBER: P3AS02R559024DE010 E3DLD1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1245840

CATALOG NUMBER: P3AS02R559024DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	103		110	107	104	102		103	100	98		99	97	96		95	94	93
2	105	100	95	91		103	98	93	90		94	91	88		91	88	86		89	86	84
3	99	91	85	81		97	90	84	80		87	82	79		85	81	77		82	79	76
4	93	84	77	72		91	83	77	72		80	75	71		78	74	70		76	73	69
5	87	77	71	66		85	76	70	65		75	69	65		73	68	64		71	67	64
6	82	72	65	60		80	71	64	60		69	64	59		68	63	59		66	62	58
7	77	67	60	55		76	66	59	55		65	59	54		63	58	54		62	57	54
8	73	62	55	51		72	62	55	51		60	55	50		59	54	50		58	53	50
9	69	58	51	47		68	58	51	47		57	51	47		56	50	46		55	50	46
10	65	55	48	44		64	54	48	44		53	47	43		52	47	43		52	47	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	34230
5°	33788
10°	32442
15°	30352
20°	27699
25°	24703
30°	21598
35°	17962
40°	14141
45°	9613
50°	5868
55°	3058
60°	2807
65°	2698
70°	2500
75°	2203
80°	2147
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9613 cd/sqm

TEST NUMBER: P1245840

CATALOG NUMBER: P3AS02R559024DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	14.4	7.9
10°-20°	37.4	20.5
20°-30°	46.8	25.7
30°-40°	41.8	23.0
40°-50°	24.5	13.4
50°-60°	8.5	4.6
60°-70°	5.1	2.8
70°-80°	2.8	1.6
80°-90°	0.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	98.6	54.2
0°-40°	140.3	77.1
0°-60°	173.2	95.2
0°-90°	182.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	182.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	156	
5°	154	14
15°	134	37
25°	102	47
35°	67	42
45°	31	24
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1245840

CATALOG NUMBER: P3AS02R559024DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	156.1
2.5°	155.2
5°	153.5
7.5°	150.0
10°	145.7
12.5°	140.4
15°	133.7
17.5°	126.6
20°	118.7
22.5°	110.5
25°	102.1
27.5°	93.7
30°	85.3
32.5°	76.3
35°	67.1
37.5°	58.0
40°	49.4
42.5°	40.2
45°	31.0
47.5°	23.6
50°	17.2
52.5°	11.2
55°	8.0
57.5°	7.1
60°	6.4
62.5°	5.8
65°	5.2
67.5°	4.5
70°	3.9
72.5°	3.2
75°	2.6
77.5°	2.1
80°	1.7
82.5°	1.1
85°	0.6
87.5°	0.4
90°	0.0

(END OF REPORT)