

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1245909

Luminaire Tested: P3AS02R709024DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245909
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R709024DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R70 optic, 2400K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 269.0 lumens
Efficiency: N/A
Efficacy: 74.7 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1245909

CATALOG NUMBER: P3AS02R709024DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1245909

CATALOG NUMBER: P3AS02R709024DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	95	87	81	77	94	86	81	76	84	79	75		82	78	75		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	76	66	59	55	75	65	59	55	64	58	55		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	50		58
10	68	58	52	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	53417
5°	50979
10°	48496
15°	47197
20°	45457
25°	43019
30°	40006
35°	33622
40°	21669
45°	10079
50°	2627
55°	650
60°	658
65°	571
70°	577
75°	508
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10079 cd/sqm

TEST NUMBER: P1245909

CATALOG NUMBER: P3AS02R709024DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.7	8.1
10°-20°	58.4	21.7
20°-30°	81.6	30.3
30°-40°	75.7	28.1
40°-50°	27.1	10.1
50°-60°	2.3	0.9
60°-70°	1.2	0.4
70°-80°	0.7	0.3
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	161.7	60.1
0°-40°	237.4	88.3
0°-60°	266.8	99.2
0°-90°	269.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	269.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	244	
5°	232	22
15°	208	58
25°	178	82
35°	126	76
45°	32	27
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1245909

CATALOG NUMBER: P3AS02R709024DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	243.6
2.5°	239.9
5°	231.6
7.5°	223.8
10°	217.8
12.5°	212.9
15°	207.9
17.5°	201.9
20°	194.8
22.5°	186.6
25°	177.8
27.5°	168.8
30°	158.0
32.5°	144.3
35°	125.6
37.5°	101.7
40°	75.7
42.5°	51.6
45°	32.5
47.5°	18.1
50°	7.7
52.5°	2.6
55°	1.7
57.5°	1.5
60°	1.5
62.5°	1.3
65°	1.1
67.5°	1.1
70°	0.9
72.5°	0.9
75°	0.6
77.5°	0.6
80°	0.4
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)