

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1245965

Luminaire Tested: P3AS05R109024DE010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245965
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-5)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R109024DE010 E3PHLP1MW
Description: 3in Adjustable LED luminaire with, R10 optic, 2400K CCT AND, 90CRI , E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 207.0 lumens
Efficiency: N/A
Efficacy: 26.2 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1245965
CATALOG NUMBER: P3AS05R109024DE010 E3PHLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1245965
 CATALOG NUMBER: P3AS05R109024DE010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90			90
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81			81
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	74			74
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68			68
5	88	78	72	67	86	77	71	67	76	70	66	74	69	65	72	68	65	63			63
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	59			59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			55
8	75	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52			52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49			49
10	69	59	52	48	68	58	52	48	57	52	48	56	51	48	56	51	48	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	77472
5°	71142
10°	56690
15°	42361
20°	32179
25°	24364
30°	18028
35°	12876
40°	8817
45°	6171
50°	5254
55°	5161
60°	5350
65°	5656
70°	5770
75°	6015
80°	6440
85°	6542

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 82.5°
 Luminance: 7560 cd/sqm



TEST NUMBER: P1245965
 CATALOG NUMBER: P3AS05R109024DE010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.6	13.8
10°-20°	52.3	25.3
20°-30°	46.4	22.4
30°-40°	30.4	14.7
40°-50°	16.2	7.8
50°-60°	12.3	5.9
60°-70°	10.5	5.1
70°-80°	7.3	3.5
80°-90°	3.0	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	127.3	61.5
0°-40°	157.7	76.2
0°-60°	186.2	89.9
0°-90°	207.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	207.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	353	
5°	323	29
15°	187	52
25°	101	46
35°	48	30
45°	20	16
55°	14	12
65°	11	11
75°	7	7
85°	3	3
90°	0	

TEST NUMBER: P1245965
CATALOG NUMBER: P3AS05R109024DE010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	353.3
2.5°	345.0
5°	323.2
7.5°	291.1
10°	254.6
12.5°	219.3
15°	186.6
17.5°	160.3
20°	137.9
22.5°	118.0
25°	100.7
27.5°	85.3
30°	71.2
32.5°	59.0
35°	48.1
37.5°	38.5
40°	30.8
42.5°	24.4
45°	19.9
47.5°	17.3
50°	15.4
52.5°	14.7
55°	13.5
57.5°	12.8
60°	12.2
62.5°	11.5
65°	10.9
67.5°	9.6
70°	9.0
72.5°	7.7
75°	7.1
77.5°	5.8
80°	5.1
82.5°	4.5
85°	2.6
87.5°	1.3
90°	0.0

(END OF REPORT)