

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1245995

Luminaire Tested: P3AS05R129024DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1245995
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R129024DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R12 optic, 2400K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 256.0 lumens
Efficiency: N/A
Efficacy: 33.7 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1245995

CATALOG NUMBER: P3AS05R129024DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1245995

CATALOG NUMBER: P3AS05R129024DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	106	111	108	106	104	104	102	101		100	99	98		97
2	108	103	98	95	105	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	93	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	110386
5°	102025
10°	81450
15°	61521
20°	46857
25°	35712
30°	25574
35°	16704
40°	10248
45°	6202
50°	4128
55°	3173
60°	2719
65°	2387
70°	2116
75°	2118
80°	1515
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6202 cd/sqm

TEST NUMBER: P1245995

CATALOG NUMBER: P3AS05R129024DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.1	16.0
10°-20°	75.8	29.6
20°-30°	67.5	26.3
30°-40°	39.9	15.6
40°-50°	16.4	6.4
50°-60°	7.7	3.0
60°-70°	4.7	1.8
70°-80°	2.5	1.0
80°-90°	0.6	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	184.3	72.0
0°-40°	224.2	87.6
0°-60°	248.3	97.0
0°-90°	256.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	256.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	503	
5°	464	41
15°	271	76
25°	148	67
35°	62	40
45°	20	16
55°	8	8
65°	5	5
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1245995

CATALOG NUMBER: P3AS05R129024DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	503.4
1°	502.2
2°	498.4
3°	491.0
4°	478.5
5°	463.5
6°	447.3
7°	428.2
8°	408.2
9°	387.9
10°	365.8
12.5°	315.5
15°	271.0
17.5°	232.8
20°	200.8
22.5°	172.5
25°	147.6
27.5°	123.5
30°	101.0
32.5°	80.6
35°	62.4
37.5°	47.8
40°	35.8
42.5°	26.6
45°	20.0
47.5°	15.4
50°	12.1
52.5°	10.0
55°	8.3
57.5°	7.1
60°	6.2
62.5°	5.4
65°	4.6
67.5°	4.2
70°	3.3
72.5°	2.9
75°	2.5
77.5°	1.7
80°	1.2
82.5°	0.8
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)