

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304887

Luminaire Tested: P3RT02R55B2750DE010 E3CBUS1MW_5000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1304887
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-92)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3RT02R55B2750DE010 E3CBUS1MW_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R55 optic, 5000K CCT AND, 80CRI , E3CBUS1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 310.0 lumens
Efficiency: N/A
Efficacy: 106.9 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 2.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1304887

CATALOG NUMBER: P3RT02R55B2750DE010 E3CBUS1MW_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1304887

CATALOG NUMBER: P3RT02R55B2750DE010 E3CBUS1MW_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10		0			
RCR																										
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102		100			
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		98	98	97		95			
2	109	105	102	99		107	103	100	97		100	98	95		97	95	93		95	93	91		90			
3	105	99	95	91		103	98	94	91		95	92	89		93	90	88		91	88	87		85			
4	100	94	89	85		99	93	88	85		91	87	84		89	86	83		87	84	82		81			
5	96	89	84	80		95	88	83	80		86	82	79		85	81	78		83	80	78		76			
6	92	84	79	76		91	84	79	75		82	78	75		81	77	74		80	76	74		73			
7	88	80	75	71		87	80	75	71		78	74	71		77	73	70		76	73	70		69			
8	85	76	71	68		84	76	71	67		75	70	67		74	70	67		73	69	67		65			
9	81	73	68	64		80	72	67	64		72	67	64		71	67	64		70	66	64		62			
10	78	70	64	61		77	69	64	61		68	64	61		68	64	61		67	63	61		59			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	102996
5°	98327
10°	98306
15°	95233
20°	86154
25°	66705
30°	33423
35°	10065
40°	2147
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 0 cd/sqm

TEST NUMBER: P1304887

CATALOG NUMBER: P3RT02R55B2750DE010 E3CBUS1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.7	13.8
10°-20°	116.3	37.5
20°-30°	119.8	38.6
30°-40°	30.2	9.7
40°-50°	1.0	0.3
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	278.8	89.9
0°-40°	309.0	99.7
0°-60°	310.0	100.0
0°-90°	310.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	310.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	470	
5°	447	43
15°	420	116
25°	276	120
35°	38	30
45°	0	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1304887

CATALOG NUMBER: P3RT02R55B2750DE010 E3CBUS1MW_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	469.7
2.5°	460.3
5°	446.7
7.5°	443.9
10°	441.5
12.5°	433.1
15°	419.5
17.5°	398.3
20°	369.2
22.5°	329.7
25°	275.7
27.5°	207.1
30°	132.0
32.5°	76.6
35°	37.6
37.5°	17.8
40°	7.5
42.5°	1.9
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)