

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246068

Luminaire Tested: P3AS05R259024DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246068
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R259024DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 2400K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 227.0 lumens
Efficiency: N/A
Efficacy: 31.5 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246068

CATALOG NUMBER: P3AS05R259024DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1246068

CATALOG NUMBER: P3AS05R259024DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	105	102	99		107	104	101	98		101	98	96		98	96	94		95	93	92
3	105	100	96	92		103	98	95	91		96	93	90		94	91	89		91	89	87
4	101	95	90	87		99	94	89	86		92	88	85		90	87	84		88	85	83
5	97	90	85	82		96	89	85	81		88	84	81		86	83	80		85	82	79
6	94	86	81	78		92	86	81	78		84	80	77		83	79	77		82	78	76
7	90	83	78	74		89	82	77	74		81	77	74		80	76	73		79	75	73
8	87	79	74	71		86	79	74	71		78	74	71		77	73	70		76	73	70
9	84	76	71	68		83	76	71	68		75	71	68		74	70	68		73	70	67
10	81	73	69	65		80	73	68	65		72	68	65		72	68	65		71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	145602
5°	135857
10°	108838
15°	73871
20°	44711
25°	26131
30°	14888
35°	8191
40°	4351
45°	2295
50°	1330
55°	994
60°	877
65°	882
70°	833
75°	763
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2295 cd/sqm

TEST NUMBER: P1246068

CATALOG NUMBER: P3AS05R259024DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.8	24.1
10°-20°	89.5	39.4
20°-30°	51.1	22.5
30°-40°	20.2	8.9
40°-50°	6.2	2.7
50°-60°	2.4	1.1
60°-70°	1.6	0.7
70°-80°	0.9	0.4
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	195.3	86.1
0°-40°	215.5	95.0
0°-60°	224.1	98.8
0°-90°	227.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	227.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	664	
5°	617	55
15°	325	89
25°	108	51
35°	31	20
45°	7	6
55°	3	2
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1246068

CATALOG NUMBER: P3AS05R259024DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	664.0
1°	662.7
2°	657.3
3°	647.8
4°	634.5
5°	617.2
6°	596.8
7°	573.8
8°	547.1
9°	519.8
10°	488.8
11°	458.2
12°	424.5
13°	391.4
14°	357.3
15°	325.4
17.5°	252.3
20°	191.6
22.5°	143.8
25°	108.0
27.5°	80.0
30°	58.8
32.5°	42.5
35°	30.6
37.5°	21.7
40°	15.2
42.5°	10.4
45°	7.4
47.5°	5.2
50°	3.9
52.5°	3.0
55°	2.6
57.5°	2.4
60°	2.0
62.5°	1.7
65°	1.7
67.5°	1.5
70°	1.3
72.5°	1.1
75°	0.9
77.5°	0.7
80°	0.4
82.5°	0.4
85°	0.2
87.5°	0.2



TEST NUMBER: P1246068

CATALOG NUMBER: P3AS05R259024DE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)