

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246112

Luminaire Tested: P3AS05R309024DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246112
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R309024DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R30 optic, 2400K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 140.0 lumens
Efficiency: N/A
Efficacy: 19.4 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246112

CATALOG NUMBER: P3AS05R309024DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1246112

CATALOG NUMBER: P3AS05R309024DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	85	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	73	90	83	77	73	81	76	72		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	74	68	64	72	67	63		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	67	61	57	75	66	60	57	65	60	56		64	60	56		63
10	73	63	58	54	72	63	57	54	62	57	53		61	57	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	47847
5°	46357
10°	41772
15°	34552
20°	26742
25°	20058
30°	14559
35°	9717
40°	5954
45°	3504
50°	2149
55°	1759
60°	1535
65°	1245
70°	1090
75°	1101
80°	884
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3504 cd/sqm

TEST NUMBER: P1246112

CATALOG NUMBER: P3AS05R309024DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.4	13.8
10°-20°	41.9	29.9
20°-30°	38.1	27.2
30°-40°	23.1	16.5
40°-50°	9.3	6.6
50°-60°	4.1	2.9
60°-70°	2.5	1.8
70°-80°	1.3	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	99.4	71.0
0°-40°	122.5	87.5
0°-60°	135.8	97.0
0°-90°	140.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	140.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	218	
5°	211	19
15°	152	42
25°	83	38
35°	36	23
45°	11	9
55°	5	4
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1246112

CATALOG NUMBER: P3AS05R309024DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	218.2
1°	218.0
2°	217.1
3°	215.6
4°	213.4
5°	210.6
6°	207.1
7°	203.4
8°	198.6
9°	193.2
10°	187.6
11°	181.0
12°	174.1
13°	167.2
14°	159.6
15°	152.2
17.5°	132.9
20°	114.6
22.5°	97.7
25°	82.9
27.5°	69.5
30°	57.5
32.5°	46.5
35°	36.3
37.5°	27.8
40°	20.8
42.5°	15.2
45°	11.3
47.5°	8.5
50°	6.3
52.5°	5.0
55°	4.6
57.5°	3.9
60°	3.5
62.5°	2.8
65°	2.4
67.5°	2.2
70°	1.7
72.5°	1.5
75°	1.3
77.5°	1.1
80°	0.7
82.5°	0.4
85°	0.4
87.5°	0.2



TEST NUMBER: P1246112
CATALOG NUMBER: P3AS05R309024DE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)