

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246117

Luminaire Tested: P3AS05R309024DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246117
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R309024DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R30 optic, 2400K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 285.0 lumens
Efficiency: N/A
Efficacy: 39.6 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246117

CATALOG NUMBER: P3AS05R309024DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1246117

CATALOG NUMBER: P3AS05R309024DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	85	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	73	90	83	77	73	81	76	72		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	74	68	64	72	67	63		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	67	61	57	75	66	60	57	65	60	56		64	60	56		63
10	73	63	58	54	72	63	57	54	62	57	54		61	57	53		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	97383
5°	94365
10°	85013
15°	70330
20°	54441
25°	40841
30°	29650
35°	19756
40°	12137
45°	7133
50°	4367
55°	3555
60°	3114
65°	2542
70°	2244
75°	2288
80°	1642
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7133 cd/sqm

TEST NUMBER: P1246117

CATALOG NUMBER: P3AS05R309024DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.4	13.8
10°-20°	85.3	29.9
20°-30°	77.6	27.2
30°-40°	46.9	16.5
40°-50°	18.8	6.6
50°-60°	8.4	2.9
60°-70°	5.0	1.8
70°-80°	2.7	1.0
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	202.4	71.0
0°-40°	249.3	87.5
0°-60°	276.5	97.0
0°-90°	285.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	285.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	444	
5°	429	39
15°	310	85
25°	169	78
35°	74	47
45°	23	19
55°	9	8
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1246117

CATALOG NUMBER: P3AS05R309024DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	444.1
1°	443.7
2°	441.9
3°	438.8
4°	434.4
5°	428.7
6°	421.6
7°	414.1
8°	404.4
9°	393.3
10°	381.8
11°	368.6
12°	354.4
13°	340.3
14°	324.8
15°	309.8
17.5°	270.5
20°	233.3
22.5°	198.9
25°	168.8
27.5°	141.4
30°	117.1
32.5°	94.6
35°	73.8
37.5°	56.6
40°	42.4
42.5°	30.9
45°	23.0
47.5°	17.2
50°	12.8
52.5°	10.2
55°	9.3
57.5°	8.0
60°	7.1
62.5°	5.7
65°	4.9
67.5°	4.4
70°	3.5
72.5°	3.1
75°	2.7
77.5°	2.2
80°	1.3
82.5°	0.9
85°	0.9
87.5°	0.4



TEST NUMBER: P1246117

CATALOG NUMBER: P3AS05R309024DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)