

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304934

Luminaire Tested: P3RT05R45B2750DE010 E3CBUS1MW\_3000K

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1304934  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-96)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3RT05R45B2750DE010 E3CBUS1MW\_3000K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R45 optic, 3000K CCT AND, 90CRI , E3CBUS1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 578.0 lumens  
Efficiency: N/A  
Efficacy: 98.0 lumens/watt  
Spacing Criteria (0/90/45): 0.67 / 0.67 / 0.63  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1304934

CATALOG NUMBER: P3RT05R45B2750DE010 E3CBUS1MW\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1304934

CATALOG NUMBER: P3RT05R45B2750DE010 E3CBUS1MW\_3000K

### COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |  |  |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|--|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |  |  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |  |  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |  |  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |  |  |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |  |  |
| 1   | 115 | 112 | 110 | 108 | 112 | 110 | 108 | 107 | 106 | 105 | 103 | 102 | 101 | 100 | 99  | 98  | 97  | 96  |  |  |
| 2   | 110 | 106 | 103 | 100 | 108 | 105 | 102 | 99  | 101 | 99  | 97  | 99  | 97  | 95  | 96  | 94  | 93  | 91  |  |  |
| 3   | 106 | 101 | 97  | 94  | 104 | 100 | 96  | 93  | 97  | 94  | 92  | 95  | 92  | 90  | 93  | 91  | 89  | 87  |  |  |
| 4   | 102 | 96  | 92  | 88  | 101 | 95  | 91  | 88  | 93  | 90  | 87  | 91  | 88  | 86  | 89  | 87  | 85  | 84  |  |  |
| 5   | 98  | 92  | 87  | 84  | 97  | 91  | 87  | 83  | 89  | 86  | 83  | 88  | 85  | 82  | 86  | 84  | 81  | 80  |  |  |
| 6   | 95  | 88  | 83  | 80  | 94  | 87  | 83  | 79  | 86  | 82  | 79  | 84  | 81  | 78  | 83  | 80  | 78  | 77  |  |  |
| 7   | 92  | 84  | 79  | 76  | 90  | 84  | 79  | 76  | 82  | 78  | 76  | 81  | 78  | 75  | 80  | 77  | 75  | 74  |  |  |
| 8   | 88  | 81  | 76  | 73  | 87  | 80  | 76  | 73  | 79  | 75  | 72  | 78  | 75  | 72  | 78  | 74  | 72  | 71  |  |  |
| 9   | 85  | 78  | 73  | 70  | 84  | 77  | 73  | 70  | 76  | 72  | 70  | 76  | 72  | 69  | 75  | 72  | 69  | 68  |  |  |
| 10  | 82  | 75  | 70  | 67  | 82  | 74  | 70  | 67  | 74  | 70  | 67  | 73  | 69  | 67  | 72  | 69  | 66  | 65  |  |  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°     |
|-----|--------|
| 0°  | 280372 |
| 5°  | 278824 |
| 10° | 262208 |
| 15° | 214326 |
| 20° | 157117 |
| 25° | 87102  |
| 30° | 34815  |
| 35° | 11350  |
| 40° | 2662   |
| 45° | 0      |
| 50° | 0      |
| 55° | 0      |
| 60° | 0      |
| 65° | 0      |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle:  $45^\circ$

Luminance: 0 cd/sqm

TEST NUMBER: P1304934

CATALOG NUMBER: P3RT05R45B2750DE010 E3CBUS1MW\_3000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 118.2  | 20.5      |
| 10°-20°   | 258.6  | 44.7      |
| 20°-30°   | 167.5  | 29.0      |
| 30°-40°   | 32.4   | 5.6       |
| 40°-50°   | 1.2    | 0.2       |
| 50°-60°   | 0.0    | 0.0       |
| 60°-70°   | 0.0    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 544.4  | 94.2      |
| 0°-40°    | 576.8  | 99.8      |
| 0°-60°    | 578.0  | 100.0     |
| 0°-90°    | 578.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 578.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1279 |      |
| 5°  | 1267 | 118  |
| 15° | 944  | 259  |
| 25° | 360  | 168  |
| 35° | 42   | 32   |
| 45° | 0    | 1    |
| 55° | 0    | 0    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P1304934

CATALOG NUMBER: P3RT05R45B2750DE010 E3CBUS1MW\_3000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1278.6 |
| 2.5°  | 1277.7 |
| 5°    | 1266.7 |
| 7.5°  | 1239.5 |
| 10°   | 1177.6 |
| 12.5° | 1072.3 |
| 15°   | 944.1  |
| 17.5° | 811.6  |
| 20°   | 673.3  |
| 22.5° | 512.8  |
| 25°   | 360.0  |
| 27.5° | 233.5  |
| 30°   | 137.5  |
| 32.5° | 78.1   |
| 35°   | 42.4   |
| 37.5° | 22.1   |
| 40°   | 9.3    |
| 42.5° | 1.7    |
| 45°   | 0.0    |
| 47.5° | 0.0    |
| 50°   | 0.0    |
| 52.5° | 0.0    |
| 55°   | 0.0    |
| 57.5° | 0.0    |
| 60°   | 0.0    |
| 62.5° | 0.0    |
| 65°   | 0.0    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |

(END OF REPORT)