

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246176

Luminaire Tested: P3AS05R409024DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246176
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R409024DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R40 optic, 2400K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 514.0 lumens
Efficiency: N/A
Efficacy: 71.4 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246176
CATALOG NUMBER: P3AS05R409024DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1246176
 CATALOG NUMBER: P3AS05R409024DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	96	96	96	94
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	91	91	91	89
3	104	99	94	91	102	97	93	90	95	91	88	92	89	87	90	88	86	86	86	86	84
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	81	81	81	80
5	96	88	83	79	94	88	83	79	86	82	78	84	81	78	83	80	77	77	77	77	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	70	70	70	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	67	67	67	65
9	82	73	68	64	81	73	68	64	72	67	64	71	67	64	70	66	64	64	64	64	63
10	78	70	65	62	78	70	65	61	69	64	61	68	64	61	67	64	61	61	61	61	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	227438
5°	220823
10°	200397
15°	165563
20°	119430
25°	73867
30°	39981
35°	20666
40°	11250
45°	6295
50°	3173
55°	2370
60°	2149
65°	2075
70°	1988
75°	1864
80°	1642
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6295 cd/sqm



TEST NUMBER: P1246176
 CATALOG NUMBER: P3AS05R409024DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.5	18.0
10°-20°	198.6	38.6
20°-30°	141.7	27.6
30°-40°	52.2	10.1
40°-50°	16.4	3.2
50°-60°	5.7	1.1
60°-70°	3.9	0.8
70°-80°	2.3	0.5
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	432.8	84.2
0°-40°	484.9	94.3
0°-60°	507.1	98.7
0°-90°	514.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	514.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1037	
5°	1003	92
15°	729	199
25°	305	142
35°	77	52
45°	20	16
55°	6	6
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1246176
CATALOG NUMBER: P3AS05R409024DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1037.2
2.5°	1029.3
5°	1003.2
7.5°	960.0
10°	900.0
12.5°	823.7
15°	729.3
17.5°	623.4
20°	511.8
22.5°	401.9
25°	305.3
27.5°	224.1
30°	157.9
32.5°	110.7
35°	77.2
37.5°	54.7
40°	39.3
42.5°	28.2
45°	20.3
47.5°	13.7
50°	9.3
52.5°	6.6
55°	6.2
57.5°	5.7
60°	4.9
62.5°	4.4
65°	4.0
67.5°	3.5
70°	3.1
72.5°	2.6
75°	2.2
77.5°	1.8
80°	1.3
82.5°	0.9
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)