

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246185

Luminaire Tested: P3AS05R459024DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246185
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R459024DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 2400K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 241.9 lumens
Efficiency: N/A
Efficacy: 33.6 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246185

CATALOG NUMBER: P3AS05R459024DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1246185

CATALOG NUMBER: P3AS05R459024DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	109	107		111	109	107	105		105	103	102		101	100	99		98	97	96
2	109	104	100	97		106	102	99	96		99	96	94		96	94	92		93	91	90
3	104	98	93	89		102	96	92	88		94	90	87		91	88	86		89	87	84
4	99	92	87	83		97	91	86	82		89	85	81		87	83	80		85	82	79
5	94	87	81	77		93	86	81	77		84	80	76		82	79	76		81	78	75
6	90	82	77	73		89	81	76	72		80	75	72		78	74	71		77	74	71
7	86	78	72	68		85	77	72	68		76	71	68		75	71	67		74	70	67
8	83	74	68	65		82	73	68	65		72	68	64		71	67	64		70	67	64
9	79	70	65	61		78	70	65	61		69	64	61		68	64	61		67	63	61
10	76	67	62	58		75	67	62	58		66	61	58		65	61	58		65	61	58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	90870
5°	88752
10°	81584
15°	69126
20°	53625
25°	37502
30°	23624
35°	13893
40°	7872
45°	3814
50°	1330
55°	1070
60°	1053
65°	986
70°	962
75°	932
80°	758
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3814 cd/sqm

TEST NUMBER: P1246185

CATALOG NUMBER: P3AS05R459024DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.3	15.4
10°-20°	83.6	34.6
20°-30°	71.0	29.4
30°-40°	33.9	14.0
40°-50°	10.2	4.2
50°-60°	2.6	1.1
60°-70°	1.9	0.8
70°-80°	1.1	0.5
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	192.0	79.3
0°-40°	225.8	93.3
0°-60°	238.6	98.6
0°-90°	241.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	241.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	414	
5°	403	37
15°	304	84
25°	155	71
35°	52	34
45°	12	10
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1246185

CATALOG NUMBER: P3AS05R459024DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	414.4
2.5°	411.8
5°	403.2
7.5°	388.3
10°	366.4
12.5°	337.4
15°	304.5
17.5°	267.9
20°	229.8
22.5°	191.1
25°	155.0
27.5°	122.1
30°	93.3
32.5°	70.1
35°	51.9
37.5°	38.3
40°	27.5
42.5°	19.0
45°	12.3
47.5°	6.9
50°	3.9
52.5°	3.0
55°	2.8
57.5°	2.6
60°	2.4
62.5°	2.2
65°	1.9
67.5°	1.7
70°	1.5
72.5°	1.3
75°	1.1
77.5°	0.9
80°	0.6
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)