

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1304960

Luminaire Tested: P3RT05R70B2750DE010 E3CBUS1MW\_3500K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1304960  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-95)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3RT05R70B2750DE010 E3CBUS1MW\_3500K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R70 optic, 3500K CCT AND, 80CRI , E3CBUS1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 504.0 lumens  
Efficiency: N/A  
Efficacy: 85.4 lumens/watt  
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.99  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1304960  
CATALOG NUMBER: P3RT05R70B2750DE010 E3CBUS1MW\_3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1304960  
 CATALOG NUMBER: P3RT05R70B2750DE010 E3CBUS1MW\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	96	95	94	94	94	94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87	87	87	87
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81	81	81	81
4	98	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76	76	76	76
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71	71	71	71
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66
7	83	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	61	61	61	61
8	79	70	64	60	78	69	64	60	68	63	59	67	62	59	66	62	59	57	57	57	57
9	75	66	60	56	74	65	60	56	64	59	56	63	59	55	63	58	55	54	54	54	54
10	72	62	56	52	71	62	56	52	61	56	52	60	55	52	59	55	52	51	51	51	51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	122578
5°	116707
10°	111643
15°	106516
20°	98499
25°	89255
30°	77050
35°	69332
40°	26965
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 0 cd/sqm



TEST NUMBER: P1304960

CATALOG NUMBER: P3RT05R70B2750DE010 E3CBUS1MW\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	49.7	9.9
10°-20°	131.1	26.0
20°-30°	167.7	33.3
30°-40°	144.8	28.7
40°-50°	10.8	2.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	348.5	69.1
0°-40°	493.3	97.9
0°-60°	504.0	100.0
0°-90°	504.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	504.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	559	
5°	530	50
15°	469	131
25°	369	168
35°	259	145
45°	0	11
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1304960  
CATALOG NUMBER: P3RT05R70B2750DE010 E3CBUS1MW\_3500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	559.0
2.5°	550.3
5°	530.2
7.5°	512.8
10°	501.4
12.5°	487.5
15°	469.2
17.5°	447.4
20°	422.1
22.5°	394.2
25°	368.9
27.5°	336.6
30°	304.3
32.5°	291.3
35°	259.0
37.5°	188.4
40°	94.2
42.5°	12.2
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)