

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246226

Luminaire Tested: P3AS05R509024DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246226
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R509024DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 2400K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 159.9 lumens
Efficiency: N/A
Efficacy: 22.2 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246226

CATALOG NUMBER: P3AS05R509024DE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1246226

CATALOG NUMBER: P3AS05R509024DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97	95	94	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		86	83	81	79
4	96	88	83	78	94	87	82	78	85	80	77		83	79	76		81	78	75	73
5	91	83	77	72	90	82	76	72	80	75	71		78	74	70		77	73	70	68
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72	68	65	64
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		69	64	61	60
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65	61	57	56
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		62	57	54	53
10	71	62	56	52	70	61	55	52	60	55	51		59	55	51		59	54	51	50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	46531
5°	45278
10°	41749
15°	36731
20°	30733
25°	24364
30°	17876
35°	12287
40°	7815
45°	4373
50°	2354
55°	1988
60°	1710
65°	1557
70°	1410
75°	1271
80°	1137
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4373 cd/sqm

TEST NUMBER: P1246226

CATALOG NUMBER: P3AS05R509024DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.1	11.9
10°-20°	44.8	28.0
20°-30°	45.8	28.7
30°-40°	29.0	18.2
40°-50°	11.6	7.2
50°-60°	4.7	2.9
60°-70°	3.0	1.9
70°-80°	1.5	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	109.7	68.6
0°-40°	138.7	86.7
0°-60°	154.9	96.9
0°-90°	159.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	159.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	212	
5°	206	19
15°	162	45
25°	101	46
35°	46	29
45°	14	12
55°	5	5
65°	3	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1246226

CATALOG NUMBER: P3AS05R509024DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	212.2
2.5°	210.7
5°	205.7
7.5°	197.9
10°	187.5
12.5°	175.2
15°	161.8
17.5°	147.0
20°	131.7
22.5°	116.3
25°	100.7
27.5°	85.1
30°	70.6
32.5°	57.6
35°	45.9
37.5°	35.9
40°	27.3
42.5°	20.1
45°	14.1
47.5°	9.5
50°	6.9
52.5°	5.8
55°	5.2
57.5°	4.5
60°	3.9
62.5°	3.5
65°	3.0
67.5°	2.6
70°	2.2
72.5°	1.7
75°	1.5
77.5°	1.1
80°	0.9
82.5°	0.6
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)