

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246258

Luminaire Tested: P3AS05R559024DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246258
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R559024DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R55 optic, 2400K CCT AND, 90CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 321.0 lumens
Efficiency: N/A
Efficacy: 44.6 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246258

CATALOG NUMBER: P3AS05R559024DE010 E3DLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1246258

CATALOG NUMBER: P3AS05R559024DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92		
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85		
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	79		
4	96	88	82	77	94	87	81	77	84	80	76	82	78	75	80	77	74	73		
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67		
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63		
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59		
8	78	68	62	57	76	67	61	57	66	61	57	65	60	57	64	60	56	55		
9	74	64	58	54	73	63	58	54	62	57	53	62	57	53	61	56	53	52		
10	70	60	55	51	69	60	54	50	59	54	50	58	54	50	58	53	50	49		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	87318
5°	85142
10°	79135
15°	70488
20°	59902
25°	48342
30°	36841
35°	26207
40°	17290
45°	10265
50°	6004
55°	3708
60°	3289
65°	2958
70°	2565
75°	2203
80°	2273
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10265 cd/sqm

TEST NUMBER: P1246258

CATALOG NUMBER: P3AS05R559024DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.9	11.2
10°-20°	86.1	26.8
20°-30°	91.2	28.4
30°-40°	61.6	19.2
40°-50°	27.0	8.4
50°-60°	9.6	3.0
60°-70°	5.7	1.8
70°-80°	3.0	0.9
80°-90°	1.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	213.2	66.4
0°-40°	274.7	85.6
0°-60°	311.4	97.0
0°-90°	321.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	321.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	398	
5°	387	36
15°	310	86
25°	200	91
35°	98	62
45°	33	27
55°	10	10
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1246258

CATALOG NUMBER: P3AS05R559024DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	398.2
2.5°	395.1
5°	386.8
7.5°	373.1
10°	355.4
12.5°	334.3
15°	310.5
17.5°	284.0
20°	256.7
22.5°	228.0
25°	199.8
27.5°	172.0
30°	145.5
32.5°	120.4
35°	97.9
37.5°	77.6
40°	60.4
42.5°	45.4
45°	33.1
47.5°	24.3
50°	17.6
52.5°	12.3
55°	9.7
57.5°	8.8
60°	7.5
62.5°	6.6
65°	5.7
67.5°	4.9
70°	4.0
72.5°	3.5
75°	2.6
77.5°	2.2
80°	1.8
82.5°	1.3
85°	0.9
87.5°	0.4
90°	0.0

(END OF REPORT)