

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246259

Luminaire Tested: P3AS05R559024DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246259
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R559024DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R55 optic, 2400K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 481.0 lumens
Efficiency: N/A
Efficacy: 66.8 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246259

CATALOG NUMBER: P3AS05R559024DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1246259

CATALOG NUMBER: P3AS05R559024DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	95	90	86	92	88	85		89	86	84		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	86	78	73	68	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	70	64	60	69	63	60		67	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	73	63	57	53	72	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	132073
5°	130728
10°	126250
15°	116709
20°	100715
25°	79529
30°	56414
35°	36379
40°	21841
45°	12311
50°	6618
55°	2370
60°	2149
65°	2075
70°	1988
75°	1864
80°	1642
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12311 cd/sqm

TEST NUMBER: P1246259

CATALOG NUMBER: P3AS05R559024DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.9	11.6
10°-20°	142.2	29.6
20°-30°	149.0	31.0
30°-40°	86.9	18.1
40°-50°	32.5	6.8
50°-60°	7.7	1.6
60°-70°	3.9	0.8
70°-80°	2.3	0.5
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	347.0	72.1
0°-40°	433.9	90.2
0°-60°	474.1	98.6
0°-90°	481.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	481.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	602	
5°	594	56
15°	514	142
25°	329	149
35°	136	87
45°	40	33
55°	6	8
65°	4	4
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1246259

CATALOG NUMBER: P3AS05R559024DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	602.3
2.5°	600.6
5°	593.9
7.5°	583.4
10°	567.0
12.5°	544.1
15°	514.1
17.5°	476.1
20°	431.6
22.5°	381.7
25°	328.7
27.5°	274.5
30°	222.8
32.5°	176.1
35°	135.9
37.5°	103.3
40°	76.3
42.5°	54.7
45°	39.7
47.5°	28.7
50°	19.4
52.5°	11.0
55°	6.2
57.5°	5.3
60°	4.9
62.5°	4.4
65°	4.0
67.5°	3.5
70°	3.1
72.5°	2.6
75°	2.2
77.5°	1.8
80°	1.3
82.5°	0.9
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)