

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246270

Luminaire Tested: P3AS05R609024DE010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246270
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R609024DE010 E3D1WH
Description: 3in Adjustable LED luminaire with, R60 optic, 2400K CCT AND, 90CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 529.0 lumens
Efficiency: N/A
Efficacy: 73.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246270
CATALOG NUMBER: P3AS05R609024DE010 E3D1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1246270
 CATALOG NUMBER: P3AS05R609024DE010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94				94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88				88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82				82
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77				77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72				72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	67				67
7	85	76	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63				63
8	81	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59				59
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56				56
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53				53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	138607
5°	130838
10°	127453
15°	124541
20°	115790
25°	103506
30°	79075
35°	45642
40°	17719
45°	7381
50°	1637
55°	229
60°	175
65°	104
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7381 cd/sqm



TEST NUMBER: P1246270
 CATALOG NUMBER: P3AS05R609024DE010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.1	10.6
10°-20°	152.8	28.9
20°-30°	191.4	36.2
30°-40°	107.0	20.2
40°-50°	20.3	3.8
50°-60°	1.0	0.2
60°-70°	0.2	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	400.3	75.7
0°-40°	507.3	95.9
0°-60°	528.7	99.9
0°-90°	529.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	529.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	632	
5°	594	56
15°	549	153
25°	428	191
35°	170	107
45°	24	20
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1246270
CATALOG NUMBER: P3AS05R609024DE010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	632.1
1°	629.5
2°	621.3
3°	611.5
4°	602.4
5°	594.4
6°	588.4
7°	583.2
8°	579.3
9°	575.6
10°	572.4
11°	569.1
12°	565.4
13°	560.9
14°	555.5
15°	548.6
16°	540.1
17°	530.6
18°	519.8
19°	507.4
20°	496.2
21°	484.1
22°	471.5
23°	458.3
24°	443.8
25°	427.8
26°	409.0
27°	388.0
28°	364.4
29°	339.3
30°	312.3
31°	285.0
32°	256.9
32.5°	241.5
33°	227.6
34°	198.9
35°	170.5
36°	145.0
37°	117.9
37.5°	105.6
38°	93.5
39°	75.3
40°	61.9
42.5°	37.7
45°	23.8



TEST NUMBER: P1246270
CATALOG NUMBER: P3AS05R609024DE010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	13.2
50°	4.8
52.5°	1.1
55°	0.6
57.5°	0.4
60°	0.4
62.5°	0.2
65°	0.2
67.5°	0.2
70°	0.2
72.5°	0.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)