

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246317

Luminaire Tested: P3AS05R659024DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246317
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R659024DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R65 optic, 2400K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 443.0 lumens
Efficiency: N/A
Efficacy: 61.5 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246317

CATALOG NUMBER: P3AS05R659024DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1246317

CATALOG NUMBER: P3AS05R659024DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	59	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	104465
5°	103213
10°	99308
15°	93031
20°	83657
25°	71036
30°	55553
35°	39592
40°	25906
45°	16033
50°	8119
55°	2867
60°	2500
65°	2542
70°	2244
75°	2203
80°	2273
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16033 cd/sqm

TEST NUMBER: P1246317

CATALOG NUMBER: P3AS05R659024DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.0	9.9
10°-20°	114.0	25.7
20°-30°	133.3	30.1
30°-40°	93.1	21.0
40°-50°	41.0	9.3
50°-60°	9.1	2.1
60°-70°	4.7	1.0
70°-80°	2.8	0.6
80°-90°	1.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	291.3	65.8
0°-40°	384.5	86.8
0°-60°	434.6	98.1
0°-90°	443.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	443.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	476	
5°	469	44
15°	410	114
25°	294	133
35°	148	93
45°	52	41
55°	8	9
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1246317

CATALOG NUMBER: P3AS05R659024DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	476.4
2.5°	474.7
5°	468.9
7.5°	459.2
10°	446.0
12.5°	429.6
15°	409.8
17.5°	385.5
20°	358.5
22.5°	328.1
25°	293.6
27.5°	257.4
30°	219.4
32.5°	182.8
35°	147.9
37.5°	117.5
40°	90.5
42.5°	68.4
45°	51.7
47.5°	38.0
50°	23.8
52.5°	12.4
55°	7.5
57.5°	6.6
60°	5.7
62.5°	5.3
65°	4.9
67.5°	4.0
70°	3.5
72.5°	3.1
75°	2.6
77.5°	2.2
80°	1.8
82.5°	1.3
85°	0.9
87.5°	0.4
90°	0.0

(END OF REPORT)