

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246326

Luminaire Tested: P3AS05R709024DE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246326
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R709024DE010 E3D1LI
Description: 3in Adjustable LED luminaire with, R70 optic, 2400K CCT AND, 90CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 526.9 lumens
Efficiency: N/A
Efficacy: 73.2 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246326
CATALOG NUMBER: P3AS05R709024DE010 E3D1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1246326

CATALOG NUMBER: P3AS05R709024DE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79			
4	95	87	82	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72			
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			
7	80	70	64	59	79	70	63	59	68	63	59	67	62	58	66	61	58	57			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45			

AVERAGE LUMINANCE (cd/sqm):

0°	102470
5°	96632
10°	91626
15°	89966
20°	86714
25°	81755
30°	81177
35°	70698
40°	45714
45°	21615
50°	3036
55°	229
60°	175
65°	208
70°	128
75°	169
80°	253
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 21615 cd/sqm



TEST NUMBER: P1246326
 CATALOG NUMBER: P3AS05R709024DE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.0	7.8
10°-20°	111.3	21.1
20°-30°	157.5	29.9
30°-40°	158.2	30.0
40°-50°	56.9	10.8
50°-60°	1.5	0.3
60°-70°	0.3	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	309.7	58.8
0°-40°	468.0	88.8
0°-60°	526.4	99.9
0°-90°	526.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	526.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	467	
5°	439	41
15°	396	111
25°	338	157
35°	264	158
45°	70	57
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1246326

CATALOG NUMBER: P3AS05R709024DE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	467.3
1°	466.0
2°	461.9
3°	455.4
4°	447.2
5°	439.0
6°	431.2
7°	425.1
8°	419.7
9°	415.4
10°	411.5
11°	408.2
12°	405.2
13°	402.2
14°	399.3
15°	396.3
16°	392.6
17°	388.7
18°	384.0
19°	378.1
20°	371.6
21°	364.5
22°	357.4
23°	350.4
24°	343.7
25°	337.9
26°	333.8
27°	330.5
28°	327.9
29°	324.9
30°	320.6
31°	314.3
32°	305.4
32.5°	300.4
33°	293.7
34°	280.5
35°	264.1
36°	245.9
37°	225.3
37.5°	215.8
38°	202.8
39°	179.7
40°	159.7
42.5°	110.6
45°	69.7



TEST NUMBER: P1246326
CATALOG NUMBER: P3AS05R709024DE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
47.5°	37.4
50°	8.9
52.5°	1.1
55°	0.6
57.5°	0.6
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.2
70°	0.2
72.5°	0.2
75°	0.2
77.5°	0.2
80°	0.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)