

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246425

Luminaire Tested: P3AS09R209024DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246425
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R209024DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R20 optic, 2400K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 249.0 lumens
Efficiency: N/A
Efficacy: 22.4 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246425

CATALOG NUMBER: P3AS09R209024DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1246425

CATALOG NUMBER: P3AS09R209024DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		90
3	100	93	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	86	79	75	92	85	79	74	82	77	73		80	76	72		78
5	89	80	73	68	87	79	73	68	77	71	67		75	70	67		73
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	59	54	74	64	58	54	63	58	54		62	57	53		61
9	72	61	55	50	70	61	55	50	60	54	50		59	54	50		58
10	68	58	51	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	61596
5°	59938
10°	55154
15°	48536
20°	41630
25°	34962
30°	28283
35°	21496
40°	15314
45°	10110
50°	6243
55°	4129
60°	3728
65°	3424
70°	3270
75°	2965
80°	2778
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10110 cd/sqm

TEST NUMBER: P1246425

CATALOG NUMBER: P3AS09R209024DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.2	10.1
10°-20°	59.5	23.9
20°-30°	66.1	26.5
30°-40°	50.4	20.2
40°-50°	25.8	10.4
50°-60°	10.6	4.3
60°-70°	6.6	2.7
70°-80°	3.7	1.5
80°-90°	1.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	150.8	60.6
0°-40°	201.2	80.8
0°-60°	237.6	95.4
0°-90°	249.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	249.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	281	
5°	272	25
15°	214	60
25°	144	66
35°	80	50
45°	33	26
55°	11	11
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1246425

CATALOG NUMBER: P3AS09R209024DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	280.9
1°	281.2
2°	279.9
3°	278.3
4°	275.8
5°	272.3
6°	268.2
7°	263.8
8°	259.0
9°	253.4
10°	247.7
12.5°	231.2
15°	213.8
17.5°	196.1
20°	178.4
22.5°	160.7
25°	144.5
27.5°	128.4
30°	111.7
32.5°	95.8
35°	80.3
37.5°	66.7
40°	53.5
42.5°	42.1
45°	32.6
47.5°	24.7
50°	18.3
52.5°	13.6
55°	10.8
57.5°	9.8
60°	8.5
62.5°	7.6
65°	6.6
67.5°	5.7
70°	5.1
72.5°	4.1
75°	3.5
77.5°	2.8
80°	2.2
82.5°	1.6
85°	0.9
87.5°	0.3
90°	0.0

(END OF REPORT)