

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246458

Luminaire Tested: P3AS09R259024DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246458
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R259024DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 2400K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 203.0 lumens
Efficiency: N/A
Efficacy: 18.3 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246458

CATALOG NUMBER: P3AS09R259024DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1246458

CATALOG NUMBER: P3AS09R259024DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	86	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	65	60	79	70	64	60	69	64	60		68	63	60		67
9	76	67	61	57	75	66	61	57	65	60	57		65	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	73700
5°	70702
10°	61945
15°	49785
20°	38247
25°	28937
30°	20915
35°	13893
40°	8416
45°	4900
50°	3138
55°	2523
60°	2237
65°	1972
70°	1603
75°	1610
80°	1137
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4900 cd/sqm

TEST NUMBER: P1246458

CATALOG NUMBER: P3AS09R259024DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.2	14.4
10°-20°	60.6	29.9
20°-30°	54.8	27.0
30°-40°	33.0	16.2
40°-50°	13.1	6.4
50°-60°	6.0	3.0
60°-70°	3.7	1.8
70°-80°	2.0	1.0
80°-90°	0.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	144.7	71.3
0°-40°	177.7	87.5
0°-60°	196.8	97.0
0°-90°	203.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	203.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	336	
5°	321	29
15°	219	61
25°	120	55
35°	52	33
45°	16	13
55°	7	6
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1246458

CATALOG NUMBER: P3AS09R259024DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	336.1
1°	336.1
2°	334.5
3°	331.0
4°	326.6
5°	321.2
6°	314.3
7°	306.4
8°	297.2
9°	288.0
10°	278.2
11°	266.8
12°	255.1
13°	243.4
14°	231.7
15°	219.3
17.5°	190.2
20°	163.9
22.5°	140.2
25°	119.6
27.5°	100.3
30°	82.6
32.5°	66.5
35°	51.9
37.5°	39.6
40°	29.4
42.5°	21.5
45°	15.8
47.5°	12.0
50°	9.2
52.5°	7.6
55°	6.6
57.5°	5.7
60°	5.1
62.5°	4.1
65°	3.8
67.5°	3.2
70°	2.5
72.5°	2.2
75°	1.9
77.5°	1.6
80°	0.9
82.5°	0.6
85°	0.6
87.5°	0.3



TEST NUMBER: P1246458

CATALOG NUMBER: P3AS09R259024DE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)