

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246478

Luminaire Tested: P3AS09R309024DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246478
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R309024DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R30 optic, 2400K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 335.0 lumens
Efficiency: N/A
Efficacy: 30.2 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246478

CATALOG NUMBER: P3AS09R309024DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1246478

CATALOG NUMBER: P3AS09R309024DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	110	105	102	99		108	104	101	98		101	98	96		98	96	94		95	93	92
3	105	100	96	92		103	98	95	91		96	93	90		94	91	89		91	89	87
4	101	95	90	87		99	94	89	86		92	88	85		90	87	84		88	85	83
5	97	90	85	82		96	89	85	81		88	84	81		86	83	80		85	82	79
6	94	86	81	78		92	85	81	77		84	80	77		83	79	76		81	78	76
7	90	82	77	74		89	82	77	74		81	76	73		80	76	73		79	75	73
8	87	79	74	71		86	79	74	71		78	73	70		77	73	70		76	72	70
9	84	76	71	68		83	75	71	68		75	70	67		74	70	67		73	70	67
10	81	73	68	65		80	73	68	65		72	68	65		71	67	65		71	67	65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	195489
5°	186066
10°	156510
15°	112872
20°	70006
25°	39825
30°	22105
35°	12019
40°	6355
45°	3442
50°	1842
55°	1223
60°	1096
65°	1141
70°	1026
75°	763
80°	758
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3442 cd/sqm

TEST NUMBER: P1246478

CATALOG NUMBER: P3AS09R309024DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.1	22.7
10°-20°	135.3	40.4
20°-30°	78.2	23.3
30°-40°	29.7	8.9
40°-50°	9.1	2.7
50°-60°	3.1	0.9
60°-70°	2.1	0.6
70°-80°	1.1	0.3
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	289.6	86.5
0°-40°	319.3	95.3
0°-60°	331.5	99.0
0°-90°	335.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	335.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	892	
5°	845	76
15°	497	135
25°	165	78
35°	45	30
45°	11	9
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1246478

CATALOG NUMBER: P3AS09R309024DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	891.5
1°	890.8
2°	885.5
3°	875.3
4°	862.7
5°	845.3
6°	823.1
7°	798.4
8°	770.9
9°	738.0
10°	702.9
11°	664.9
12°	624.7
13°	582.6
14°	539.9
15°	497.2
17.5°	392.1
20°	300.0
22.5°	222.5
25°	164.6
27.5°	119.6
30°	87.3
32.5°	63.0
35°	44.9
37.5°	31.3
40°	22.2
42.5°	15.5
45°	11.1
47.5°	7.6
50°	5.4
52.5°	3.8
55°	3.2
57.5°	2.8
60°	2.5
62.5°	2.2
65°	2.2
67.5°	1.9
70°	1.6
72.5°	1.3
75°	0.9
77.5°	0.9
80°	0.6
82.5°	0.6
85°	0.3
87.5°	0.0



TEST NUMBER: P1246478

CATALOG NUMBER: P3AS09R309024DE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)