

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246480

Luminaire Tested: P3AS09R309024DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246480
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R309024DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R30 optic, 2400K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 683.0 lumens
Efficiency: N/A
Efficacy: 61.5 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246480

CATALOG NUMBER: P3AS09R309024DE010 E3DL1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1246480

CATALOG NUMBER: P3AS09R309024DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	105	102	99	107	104	101	98	101	98	96		98	96	94		95
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91
4	101	95	90	87	99	94	89	86	92	88	85		90	87	84		88
5	97	90	85	82	96	89	85	81	88	84	81		86	83	80		85
6	94	86	81	78	92	85	81	77	84	80	77		83	79	76		81
7	90	82	77	74	89	82	77	74	81	76	73		80	76	73		79
8	87	79	74	71	86	79	74	71	78	73	70		77	73	70		76
9	84	76	71	68	83	75	71	68	75	70	67		74	70	67		73
10	81	73	68	65	80	73	68	65	72	68	65		71	67	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	398543
5°	379330
10°	319077
15°	230103
20°	142742
25°	81174
30°	45096
35°	24521
40°	12939
45°	7008
50°	3753
55°	2485
60°	2281
65°	2335
70°	2052
75°	1610
80°	1642
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7008 cd/sqm

TEST NUMBER: P1246480

CATALOG NUMBER: P3AS09R309024DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.2	22.7
10°-20°	275.8	40.4
20°-30°	159.4	23.3
30°-40°	60.5	8.9
40°-50°	18.6	2.7
50°-60°	6.3	0.9
60°-70°	4.2	0.6
70°-80°	2.3	0.3
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	590.4	86.4
0°-40°	651.0	95.3
0°-60°	675.8	98.9
0°-90°	683.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	683.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1818	
5°	1723	155
15°	1014	276
25°	336	159
35°	92	61
45°	23	19
55°	6	6
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1246480

CATALOG NUMBER: P3AS09R309024DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1817.5
1°	1816.3
2°	1805.3
3°	1784.6
4°	1758.8
5°	1723.3
6°	1678.2
7°	1627.9
8°	1571.7
9°	1504.6
10°	1433.0
11°	1355.6
12°	1273.6
13°	1187.8
14°	1100.7
15°	1013.6
17.5°	799.4
20°	611.7
22.5°	453.6
25°	335.5
27.5°	243.9
30°	178.1
32.5°	128.4
35°	91.6
37.5°	63.9
40°	45.2
42.5°	31.6
45°	22.6
47.5°	15.5
50°	11.0
52.5°	7.7
55°	6.5
57.5°	5.8
60°	5.2
62.5°	4.5
65°	4.5
67.5°	3.9
70°	3.2
72.5°	2.6
75°	1.9
77.5°	1.9
80°	1.3
82.5°	1.3
85°	0.6
87.5°	0.0



TEST NUMBER: P1246480
CATALOG NUMBER: P3AS09R309024DE010 E3DL1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)