

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246512

Luminaire Tested: P3AS09R359024DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246512
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R359024DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R35 optic, 2400K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 256.0 lumens
Efficiency: N/A
Efficacy: 23.1 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246512
CATALOG NUMBER: P3AS09R359024DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1246512
 CATALOG NUMBER: P3AS09R359024DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	58482
5°	57231
10°	53595
15°	48127
20°	41864
25°	35663
30°	29878
35°	23798
40°	17204
45°	10885
50°	5936
55°	4129
60°	3903
65°	3632
70°	3462
75°	2965
80°	2778
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10885 cd/sqm



TEST NUMBER: P1246512
 CATALOG NUMBER: P3AS09R359024DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.2	9.5
10°-20°	59.0	23.0
20°-30°	67.6	26.4
30°-40°	55.1	21.5
40°-50°	27.8	10.9
50°-60°	10.4	4.0
60°-70°	6.9	2.7
70°-80°	3.8	1.5
80°-90°	1.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	150.8	58.9
0°-40°	205.9	80.4
0°-60°	244.1	95.3
0°-90°	256.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	256.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	267	
5°	260	24
15°	212	59
25°	147	68
35°	89	55
45°	35	28
55°	11	10
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1246512
CATALOG NUMBER: P3AS09R359024DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	266.7
1°	266.4
2°	265.7
3°	264.5
4°	262.6
5°	260.0
6°	256.9
7°	253.7
8°	249.6
9°	245.5
10°	240.7
11°	235.7
12°	230.3
13°	224.3
14°	218.0
15°	212.0
17.5°	195.8
20°	179.4
22.5°	162.6
25°	147.4
27.5°	132.5
30°	118.0
32.5°	103.4
35°	88.9
37.5°	74.3
40°	60.1
42.5°	46.8
45°	35.1
47.5°	25.3
50°	17.4
52.5°	12.7
55°	10.8
57.5°	9.8
60°	8.9
62.5°	7.9
65°	7.0
67.5°	6.0
70°	5.4
72.5°	4.4
75°	3.5
77.5°	2.8
80°	2.2
82.5°	1.6
85°	0.9
87.5°	0.6



TEST NUMBER: P1246512
CATALOG NUMBER: P3AS09R359024DE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)