

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246523

Luminaire Tested: P3AS09R359024DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246523
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R359024DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R35 optic, 2400K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 419.0 lumens
Efficiency: N/A
Efficacy: 37.7 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246523

CATALOG NUMBER: P3AS09R359024DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1246523

CATALOG NUMBER: P3AS09R359024DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	97	93	97	94	91		94	92	89		91
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86
4	97	89	83	79	95	88	82	78	86	81	77		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	77	72	68	76	71	67		75	70	67		73
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	70	64	60	78	69	63	59	68	63	59		67	62	59		66
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	134682
5°	131367
10°	120082
15°	101930
20°	80694
25°	61044
30°	44437
35°	30062
40°	18463
45°	10606
50°	6379
55°	5161
60°	4517
65°	3995
70°	3334
75°	3304
80°	3283
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10606 cd/sqm

TEST NUMBER: P1246523

CATALOG NUMBER: P3AS09R359024DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.1	13.2
10°-20°	123.8	29.5
20°-30°	115.8	27.6
30°-40°	70.9	16.9
40°-50°	27.9	6.7
50°-60°	12.3	2.9
60°-70°	7.6	1.8
70°-80°	4.1	1.0
80°-90°	1.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	294.7	70.3
0°-40°	365.6	87.3
0°-60°	405.9	96.9
0°-90°	419.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	419.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	614	
5°	597	55
15°	449	124
25°	252	116
35°	112	71
45°	34	28
55°	14	12
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1246523

CATALOG NUMBER: P3AS09R359024DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	614.2
1°	614.8
2°	612.9
3°	609.0
4°	603.2
5°	596.8
6°	588.4
7°	578.7
8°	567.1
9°	554.2
10°	539.3
11°	523.9
12°	507.1
13°	489.0
14°	469.0
15°	449.0
17.5°	397.4
20°	345.8
22.5°	296.1
25°	252.3
27.5°	211.6
30°	175.5
32.5°	141.9
35°	112.3
37.5°	85.8
40°	64.5
42.5°	46.5
45°	34.2
47.5°	24.5
50°	18.7
52.5°	15.5
55°	13.5
57.5°	11.6
60°	10.3
62.5°	9.0
65°	7.7
67.5°	6.5
70°	5.2
72.5°	4.5
75°	3.9
77.5°	3.2
80°	2.6
82.5°	1.9
85°	1.3
87.5°	0.6



TEST NUMBER: P1246523

CATALOG NUMBER: P3AS09R359024DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)