

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246603

Luminaire Tested: P3AS09R509024DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246603
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R509024DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R50 optic, 2400K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 565.0 lumens
Efficiency: N/A
Efficacy: 50.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246603

CATALOG NUMBER: P3AS09R509024DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1246603

CATALOG NUMBER: P3AS09R509024DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91		
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83		
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75		
4	93	85	78	73	91	83	77	73	81	76	72	79	75	71	77	73	70	69		
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63		
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58		
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	53		
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50		
9	70	59	53	48	69	59	52	48	58	52	48	57	52	48	56	51	48	46		
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	114815
5°	113119
10°	108125
15°	100137
20°	89981
25°	79093
30°	67276
35°	54556
40°	40991
45°	26390
50°	12554
55°	9863
60°	9341
65°	8717
70°	7886
75°	7117
80°	6566
85°	6542

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 26390 cd/sqm

TEST NUMBER: P1246603

CATALOG NUMBER: P3AS09R509024DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.2	8.5
10°-20°	123.0	21.8
20°-30°	149.4	26.4
30°-40°	126.7	22.4
40°-50°	65.8	11.6
50°-60°	23.8	4.2
60°-70°	16.4	2.9
70°-80°	8.9	1.6
80°-90°	2.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	320.6	56.7
0°-40°	447.3	79.2
0°-60°	536.8	95.0
0°-90°	565.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	565.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	524	
5°	514	48
15°	441	123
25°	327	149
35°	204	127
45°	85	66
55°	26	24
65°	17	16
75°	8	9
85°	3	3
90°	0	

TEST NUMBER: P1246603

CATALOG NUMBER: P3AS09R509024DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	523.6
2.5°	521.7
5°	513.9
7.5°	502.3
10°	485.6
12.5°	464.3
15°	441.1
17.5°	414.6
20°	385.6
22.5°	356.0
25°	326.9
27.5°	296.6
30°	265.7
32.5°	234.7
35°	203.8
37.5°	173.5
40°	143.2
42.5°	114.1
45°	85.1
47.5°	56.7
50°	36.8
52.5°	28.4
55°	25.8
57.5°	23.2
60°	21.3
62.5°	18.7
65°	16.8
67.5°	14.2
70°	12.3
72.5°	10.3
75°	8.4
77.5°	6.4
80°	5.2
82.5°	3.9
85°	2.6
87.5°	1.3
90°	0.0

(END OF REPORT)