

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1246609

Luminaire Tested: P3AS09R509024DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1246609
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R509024DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R50 optic, 2400K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 477.0 lumens
Efficiency: N/A
Efficacy: 43.0 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1246609

CATALOG NUMBER: P3AS09R509024DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1246609

CATALOG NUMBER: P3AS09R509024DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		86
4	96	88	82	78	94	87	82	78	85	80	77		83	79	76		81
5	91	83	76	72	90	82	76	72	80	75	71		78	74	70		77
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	138739
5°	134999
10°	124491
15°	109490
20°	91591
25°	72633
30°	53299
35°	36647
40°	23272
45°	13025
50°	7062
55°	5926
60°	5087
65°	4670
70°	4167
75°	3813
80°	3283
85°	3271

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13025 cd/sqm

TEST NUMBER: P1246609

CATALOG NUMBER: P3AS09R509024DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.8	11.9
10°-20°	133.6	28.0
20°-30°	136.6	28.6
30°-40°	86.6	18.2
40°-50°	34.5	7.2
50°-60°	14.0	2.9
60°-70°	8.9	1.9
70°-80°	4.6	1.0
80°-90°	1.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	327.0	68.6
0°-40°	413.6	86.7
0°-60°	462.1	96.9
0°-90°	477.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	477.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	633	
5°	613	57
15°	482	134
25°	300	137
35°	137	87
45°	42	34
55°	16	14
65°	9	9
75°	4	5
85°	1	1
90°	0	

TEST NUMBER: P1246609

CATALOG NUMBER: P3AS09R509024DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	632.7
2.5°	628.2
5°	613.3
7.5°	590.1
10°	559.1
12.5°	522.3
15°	482.3
17.5°	438.4
20°	392.5
22.5°	346.7
25°	300.2
27.5°	253.7
30°	210.5
32.5°	171.7
35°	136.9
37.5°	107.2
40°	81.3
42.5°	60.0
45°	42.0
47.5°	28.4
50°	20.7
52.5°	17.4
55°	15.5
57.5°	13.6
60°	11.6
62.5°	10.3
65°	9.0
67.5°	7.7
70°	6.5
72.5°	5.2
75°	4.5
77.5°	3.2
80°	2.6
82.5°	1.9
85°	1.3
87.5°	0.6
90°	0.0

(END OF REPORT)